

Data Sheet

RT015xxVDWC

Page 1/4


P/N

310631xx

xx=number of poles

2014/06/17

Illustration



see enlarged drawing at the end of the document

Product specification

- screw type terminal block, solderable
- centerline 5.00 mm, direction of connection vertical 0°
- wire protector, fittable without loss of poles
- color gray
- Connection data

CRIUS V / A / AWG 300 / 15 / 22 - 14

SEV 1.5 mm² 130 V / 13 A / T60

Data Sheet

RT015xxVDWC

Page 2/4

P/N

310631xx

xx=number of poles

2014/06/17

Technical Data

General Data

Tightening torque SEV	0.4 Nm		
Tightening torque UL	3.5 lb-in		
Solder pin length	3.4 mm		
min. number of poles	2		
max. number of poles	22		
Insulating material class	CTI 600		
clearance/creepage dist.	2.6 mm		
protection category	IP 10		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Rated voltage	200 V	500 V	500 V
Rated test voltage	2.5 kV	2.5 kV	2.5 kV

Connection data

extended wiring UL Wire range extended to No. 30 AWG for factory-wiring. Two same size wires No. 22-18 AWG Cu Sol/Str for field-wiring; No. 30-18 Cu Sol/Str factory-wiring.

 V / A / AWG 300 / 15 / 22 - 14

 1.5 mm² 130 V / 13 A / T60

Material

insulating material	PA66
flammability class	V0
terminal body material	CuZn
terminal body surface	Ni + Sn
screw surface	Zn Cr(VI)-frei/free
wire protector material	CuSn
wire protector surface	Sn
screw thread	M3

Climatic properties

upper limit temperature	105 °C
lower limit temperature	-40 °C

General

solderability	Acc. to JEDEC JESD22-B102E 245°C/5s
Tolerance	ISO 2768 -mH

Data Sheet

RT015xxVDWC

Page 3/4

P/N


310631xx

xx=number of poles

2014/06/17

Illustration

Drawing



$$L = (\text{pole size} - 1) \times \text{centerline} + 5 [0.197]$$



Data Sheet

RT015xxVDWC

Page 4/4

P/N

310631xx

xx=number of poles

2014/06/17

PCB Layout

