




Wire & Cable > High Speed Digital & Data Cable



Cable Type: **Cheminax**
Impedance: **50 Ω**
Wire Size: **26 AWG**
Operating Temperature Range: **-65 – 125 °C [-85 – 257 °F]**

Features

Product Type Features

Cable Style	Round Braided
-------------	---------------

Electrical Characteristics

Capacitance	.0000308 pF/m[30.8 pF/ft]
Impedance	50 Ω

Signal Characteristics

Velocity of Propagation	66 %
-------------------------	------

Body Features

Jacket Material	Thermorad S
Shield Type	Single
Conductor Material	Silver-Plated High Strength Copper
Cable Color	Black
Shield Plating Material	Tin
Shield Material	Copper

Dimensions

Conductor Diameter Range	.48 mm[.019 in]
Outside Cable Diameter	2.44 mm[.096 in]
Cable Dielectric Diameter	1.5 mm[.059 in]
Wire Size	26 AWG



Usage Conditions

Cable Type	Cheminax
Operating Temperature Range	-65 – 125 °C[-85 – 257 °F]

Other

Dielectric Material	Rayolin, Rayolin F
---------------------	--------------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量超出标准 Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Cd (.6% in conductor) Article Safe Usage Statements: Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Out of Scope - excluded from Halogen requirements
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought



Documents

Datasheets & Catalog Pages
Raychem Cheminax RF Coaxial Cables and RF Connectors Selection Guide
English

Product Specifications
Product Specification
English