

Data Sheet

RT043xxLBLC

Page 1/4


P/N

313051xx

xx=number of poles

2015/03/16

Illustration



see enlarged drawing at the end of the document

Product specification

- screw type terminal block, solderable
- centerline 3.50 mm, direction of connection 35°
- lift system, fittable without loss of poles
- color black
- Connection data

CRIUS V / A / AWG 300 / 10 / 28 - 16

SEV 1.0 mm² 130 V / 13.5 A / T60

Data Sheet



RT043xxLBLC

Technical Data

General Data

Tightening torque SEV	0.25 Nm		
Tightening torque UL	3 lb-in		
Solder pin length	3.5 mm		
min. number of poles	2		
max. number of poles	24		
Insulating material class	CTI 600		
clearance/creepage dist.	2.6 mm		
protection category	IP 20		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Rated voltage	200 V	500 V	500 V
Rated test voltage	2.5 kV	2.5 kV	2.5 kV

Connection data

 V / A / AWG	300 / 10 / 28 - 16		
 1.0 mm ²	130 V / 13.5 A / T60		

Material

insulating material	PA66
flammability class	V0
contact material	CuSn
contact surface	Sn
terminal body material	CuZn
terminal body surface	Ni
screw surface	Zn Cr(VI)-frei/free
screw thread	M2

Climatic properties

upper limit temperature	105 °C
lower limit temperature	-40 °C

General

solderability	Acc. to JEDEC JESD22-B102E 245°C/5s
Tolerance	ISO 2768 -mH



Data Sheet

RT043xxLBLC

Page 3/4

P/N


313051xx

xx=number of poles

2015/03/16

Illustration

Drawing



$$L = (\text{pole size} - 1) \times \text{centerline} + 3.5 [0.138]$$



Data Sheet

RT043xxLBLEC

Page 4/4

P/N

313051xx

xx=number of poles

2015/03/16

PCB Layout

