


# SPECIFICATION CONTROL DRAWING

**55A6213**

TITLE ONE CONDUCTOR CABLE, SHIELDED, JACKETED, GENERAL PURPOSE, 600 VOLT	Date 11-19-12	Revision B
This specification sheet forms a part of the latest issue of Raychem Specification 55A.		



CABLE CONSTRUCTION DETAILS							
PART NUMBER <i>1/</i>	CONDUCTOR SIZE (AWG)	SHIELD SIZE (AWG)	JACKET THICKNESS (inches)		OUTSIDE DIAMETER (inches)		MAXIMUM WEIGHT (lbs/1000 ft.)
			MINIMUM	MAXIMUM	NOMINAL	MAXIMUM	
55A6213-24-*	24	38	.005	.010	.078	.084	6.6
55A6213-22-*	22	38	.005	.010	.083	.089	7.8
55A6213-20-*	20	38	.005	.010	.091	.098	9.9
55A6213-18-*	18	38	.005	.010	.103	.111	13.3
55A6213-16-*	16	38	.005	.010	.110	.118	15.6
55A6213-14-*	14	38	.005	.010	.127	.135	21.7
55A6213-12-*	12	38	.005	.010	.144	.152	29.6
55A6213-10-*	10	38	.006	.011	.167	.180	43.2

### CABLE RATINGS AND ADDITIONAL REQUIREMENTS

**TEMPERATURE RATING:** 150°C  
 Maximum continuous conductor temperature  
**VOLTAGE RATING:** 600 volts (rms) at sea level  
**BLOCKING:** 200 ± 3°C for 6 hours  
**CROSSLINKED VERIFICATION:** 300 ± 5°C for 6 hours  
**DIELECTRIC WITHSTAND:** 1500 volts (rms), 60 Hz  
**FLAMMABILITY (Procedure 1):** 3 seconds (maximum);  
 3 in. (maximum); no flaming of facial tissue  
**JACKET COLOR:** White preferred  
**JACKET ELONGATION AND TENSILE STRENGTH:**  
 Elongation, 50% (minimum)  
 Tensile Strength, 5000 lbf/in<sup>2</sup> (minimum)  
**JACKET FLAWS:**  
 Spark Test, 1.5 kV (rms)  
 Impulse Dielectric Test, 6.0 kV (peak)

**LOW TEMPERATURE-COLD BEND:** -55 ± 5°C for 4 hours  
**SHIELD COVERAGE:** 85% (minimum)  
**VOLTAGE WITHSTAND (Post Environmental):**  
 1000 volts (rms), 60 Hz, 1 minute

**PART NUMBER:**  
 The "\*" in the part numbers above shall be replaced by color code designators with a dash separating the component wire color from the jacket color.

*1/* Example: AWG 20, white component wire; white jacket:  
 55A6213-20-9-9

**NOTE:** Nominal values are for information only.  
 Nominal values are not requirements.

This cable shall meet all constructional requirements of M27500 (AWGSM1T23).

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice. Tyco Electronics Corporation also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.		
1/ COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. HOWEVER, DUE TO LENGTH LIMITATIONS OF THE RAYCHEM PART NUMBER, AN ALTERNATIVE COLOR CODE MAY REPLACE MIL-STD-681 COLOR CODE DESIGNATORS. (EXAMPLE: "901/902..." MAY BE REPLACED BY "Axxx".) OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.		
Page 1 of 1	Raychem, TE Connectivity, TE connectivity (logo) and TE (logo) are trademarks. DIMENSIONS ARE IN INCHES, AND UNLESS OTHERWISE DESIGNATED ARE NOMINAL. THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN. REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.	<p style="font-size: x-small;">                     Raychem Wire &amp; Cable                      501 Oakside Avenue                      Redwood City, CA 94063-3800                      Phone: 1-800-227-8816                      Fax: 1-650-361-6297                 </p>