






holder, 3-way, plastic, 1 NC, LED module, red, 6-24 V AC/DC, screw terminal

product brand name	SIRIUS ACT
product designation	Holders
design of the product	holder for plastic
product type designation	3SU1
manufacturer's article number	
<ul style="list-style-type: none"> • of supplied contact module • of supplied contact module at position 1 • of supplied LED module • of the supplied holder 	3SU1400-1AA10-1CA0 3SU1400-1AA10-1CA0 3SU1401-1BG20-1AA0 3SU1500-0AA10-0AA0
Actuator	
design of the actuating element	3-way with module
number of contact modules	1
Holder	
material of the holder	Plastic
Display	
number of LED modules	1
General technical data	
product function positive opening	Yes
product component	
<ul style="list-style-type: none"> • diode • lamp transformer • light source • series resistor 	Yes No Yes No
insulation voltage rated value	320 V
degree of pollution	3
surge voltage resistance rated value	4 kV
protection class IP of the terminal	IP20
shock resistance	
<ul style="list-style-type: none"> • according to IEC 60068-2-27 • for railway applications according to EN 61373 	sinusoidal half-wave 15g / 11 ms Category 1, Class B
vibration resistance	
<ul style="list-style-type: none"> • according to IEC 60068-2-6 • for railway applications according to EN 61373 	10 ... 500 Hz: 5g Category 1, Class B
operating frequency maximum	3 600 1/h
mechanical service life (operating cycles) typical	10 000 000
thermal current	10 A
reference code according to IEC 81346-2	U
continuous current of the C characteristic MCB	10 A; for a short-circuit current smaller than 400 A
continuous current of the quick DIAZED fuse link	10 A
continuous current of the DIAZED fuse link gG	10 A

Substance Prohibitance (Date)	10/01/2014				
operating voltage					
• at AC					
— at 50 Hz rated value	6 ... 24 V				
— at 60 Hz rated value	6 ... 24 V				
• at DC rated value	6 ... 24 V				
Power Electronics					
contact reliability	One maloperation per 100 million (17 V, 5 mA), one maloperation per 10 million (5 V, 1 mA)				
Control circuit/ Control					
inrush current of LED module maximum	2 A				
Auxiliary circuit					
design of the contact of auxiliary contacts	Silver alloy				
number of NC contacts for auxiliary contacts	1				
number of NO contacts for auxiliary contacts	0				
operational current at AC-15 at 230 V rated value	6 A				
Connections/ Terminals					
type of electrical connection					
• of modules and accessories	Screw-type terminal				
type of connectable conductor cross-sections					
• solid with core end processing	2x (0.5 ... 0.75 mm ²)				
• solid without core end processing	2x (1.0 ... 1.5 mm ²)				
• finely stranded with core end processing	2x (0.5 ... 1.5 mm ²)				
• finely stranded without core end processing	2x (1,0 ... 1,5 mm ²)				
• for AWG cables	2x (18 ... 14)				
tightening torque of the screws in the bracket	1 ... 1.2 N·m				
tightening torque					
• with screw-type terminals	0.8 ... 0.9 N·m				
Lamp					
type of light source	LED				
color of the light source	red				
light intensity	450 ... 1 120 mcd				
Ambient conditions					
ambient temperature					
• during operation	-25 ... +70 °C				
• during storage	-40 ... +80 °C				
environmental category during operation according to IEC 60721	3M6, 3S2, 3B2, 3K6 (with relative air humidity of 10 ... 95%, no condensation in operation permitted)				
Installation/ mounting/ dimensions					
fastening method	front plate mounting				
• of modules and accessories	Front plate mounting				
height	40 mm				
width	30 mm				
shape of the installation opening	round				
installation width	30 mm				
installation depth	49.8 mm				
thickness of the front plate usable	1 ... 6 mm				
Certificates/ approvals					
General Product Approval	Declaration of Con- formity				
	Confirmation				
Declaration of Con- formity	Test Certificates	other	Environment		

Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1501-1AG20-1CA0>

Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1501-1AG20-1CA0>


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SU1501-1AG20-1CA0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1501-1AG20-1CA0&lang=en





last modified:

6/25/2022 