



[Products](#) ▾ [Documentation](#) ▾ [Resources](#) ▾ [My Account](#) ▾ [Customer Support](#)**TXR54AB00-1610AI2 Product Details****TXR54AB00-1610AI2**

TE Internal Number: 371807-000

**Braid, Fixed, Spin and Tinel Lock Adapters**[Not EU RoHS or ELV Compliant](#)**Product Highlights:**

- Style = Tinel Lock Braided
- Connector Code = 54
- Straight
- Shell Size = 16, 16S, 19
- Entry Size = 10

[View all Features](#)**Quick Links**

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)[Request Sample](#)[Find Similar Products](#)[Buy Product](#)

Documentation & Additional Information	
Product Drawings: • Tinel-Lock Adapter (PDF, English) Catalog Pages/Data Sheets: • None Available Product Specifications: • None Available Application Specifications: • None Available Instruction Sheets: • None Available CAD Files: • None Available	Additional Information: • Product Line Information Related Products: • Tooling
List all Documents	

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: • Style = Tinel Lock Braided • Shell Size = 16, 16S, 19 • Material = Aluminum Alloy • Finish = Cadmium Plating over Electroless Nickel • Color = Olive Drab Electrical Characteristics: • Angle = Straight • Entry Size = 10 • Boot Diameter (mm [in]) = 23.49 [0.925] • Entry Diameter (mm [in]) = 15.87 [0.625] • Finish Code = B	Body Related Features: • Connector Code = 54 • Cable Diameter (Max.) (mm [in]) = 15.37 [0.605] Configuration Related Features: • Braid = Preattached Single 36 AWG Braid • Material Code = A Industry Standards: • RoHS/ELV Compliance = Not ELV/RoHS compliant • Lead Free Solder Processes = Not relevant for lead free process Other: • Brand = Raychem

[Provide Website Feedback](#) | [Need Help?](#)[Home](#) | [Customer Support](#) | [Suppliers](#) | [Site Map](#) | [Privacy Policy](#) | [Browser Support](#)
© 2009 Tyco Electronics Corporation All Rights Reserved