

Data sheet

Page 1/5

OpDAT REGplus 2xSC/ST-D MM (Ph-Br), 1xM20, with shrink splice holder P/N

150240C30210S


EAN 4250184152552

2015-28-05

Illustrations



Dimensional drawing



See enlarged drawings at the end of document

Product specification

- splice distributor for TH35 rail
- equipped with SC-D/ST-D (MM) couplers made of zinc die-casting
- slotted metal sleeve (Ph-Br) for multi mode applications
- with fiber reservoir
- custom-labeled identification strips
- various mounting versions on rail
- splice tray with shrink splice holder
- front plate can be completely removed
- cable feed from top or bottom, straight or inclined, with M20 cable gland (up to 2 possible)
- feed of preassembled cables is possible
- one cable gland M20 with strain relief included in the delivery
- housing cover fastening by means of just one captive screw
- unoccupied coupler recesses are closed with special blind plugs
- variants: equipped with 2, 3, 4 or 6 SC-D/ST-D couplers (SC-D interior, ST-D exterior)
- please note: if you use preassembled cables with ST plugs, use the unequipped version of the OpDAT REG plus. The ST-D couplers required in this case are available as accessory. Before mounting the couplers in the housing, plug the preassembled ST plugs in the couplers for reasons of space.



Data sheet

Page 2/5

OpDAT REGplus 2xSC/ST-D MM (Ph-Br), 1xM20, with shrink splice holder

P/N

150240C30210S

EAN 4250184152552

2015-28-05

Technical Data

General Data

Fields of application

Structured building cabling

Design

Splice distributor

Mounting style

Standard rail TH35

Color

gray

Dimensions

Dimension (L x W x H)

144.80 x 143.80 x 37.00 mm

Dimension (L x W x H)

5.70 x 5.66 x 1.46 in.

Mode type of the fiber

Multimode

Labeling option

identification label

Connections/interfaces

Connector technology interface 1 SC-D/ST-D Couplers

Connector technology interface 2 SC-D/ST-D Couplers

Number of ports interface 1 6

Number of ports interface 2 6

Number of equipped ports interface 1 2

Number of ports interface 2 equipped 2

Number of ports with dust protection interface 1 2

Number of ports with dust protection interface 2 2

Number of blind covers interface 2 4

Cable access/outlet from top or bottom, straight or inclined

Mechanical characteristics

Cut-out SC-D, LC-Q, ST-D

Connector type Duplex

Life - Number of mating cycles min. 500

Strain relief M Verschraubung

Materials and material properties

Material - Coupler housing GD-Zn (zinc die-cast)

Material - Front cover Frianyl

Material - Sleeve PhBr, slotted



Data sheet

Page 3/5

OpDAT REGplus 2xSC/ST-D MM (Ph-Br), 1xM20, with shrink splice holder P/N

150240C30210S

EAN 4250184152552

2015-28-05

Technical Data

Certifications

Gost Certification yes

Approvals

RoHS compliant

Classifications

ETIM 5.0 EC001130

Packing details

Type of packaging	1 pc(s) / box
Packaging unit - Weight (gram)	636.00 g
Packaging unit - Weight (pound)	1.40 lb
Packaging dimension (W x H x D)	145.00 x 182.00 x 40.00 mm
Packaging dimension (W x H x D)	5.71 x 7.17 x 1.57 in.



Data sheet

Page 4/5

OpDAT REGplus 2xSC/ST-D MM (Ph-Br), 1xM20, with shrink splice holder P/N**150240C30210S****EAN 4250184152552**

2015-28-05

Accessories

P/N	Designation
899789-01	Label sheet for E-DAT C6 and E-DAT design patch panels



Data sheet

Page 5/5

OpDAT REGplus 2xSC/ST-D MM (Ph-Br), 1xM20, with shrink splice holder P/N

150240C30210S

EAN 4250184152552

2015-28-05

Illustrations

Dimensional drawing

