

SIMATIC DP, Electronics module for ET 200SP, F-DI 8x 24 V DC HF, 15 mm width, up to PL E (ISO 13849-1)/ SIL3 (IEC 61508)



General information	
Product type designation	F-DI 8x24VDC HF
usable BaseUnits	BU type A0
Product function	
<ul style="list-style-type: none"> <li>I&amp;M data</li> </ul>	Yes; I&M0 to I&M3
Engineering with	
<ul style="list-style-type: none"> <li>STEP 7 TIA Portal configurable/integrated as of version</li> </ul>	V12
<ul style="list-style-type: none"> <li>STEP 7 configurable/integrated as of version</li> </ul>	V5.5 SP3 / -
<ul style="list-style-type: none"> <li>PROFINET as of GSD version/GSD revision</li> </ul>	V2.31
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	20.4 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Input current	
Current consumption (rated value)	75 mA; without load
Current consumption, max.	21 mA; From the backplane bus

Encoder supply	
Number of outputs	8
Short-circuit protection	Yes; Electronic (response threshold 0.7 A to 1.8 A)
Output current	
<ul style="list-style-type: none"> <li>• up to 60 °C, max.</li> </ul>	0.3 A
24 V encoder supply	
<ul style="list-style-type: none"> <li>• 24 V</li> </ul>	Yes; min. L+ (-1.5 V)
<ul style="list-style-type: none"> <li>• Short-circuit protection</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• Output current, max.</li> </ul>	800 mA; Total current of all encoders
Power	
Power available from the backplane bus	70 mW
Power loss	
Power loss, typ.	4 W
Address area	
Address space per module	
<ul style="list-style-type: none"> <li>• Inputs</li> </ul>	6 byte
<ul style="list-style-type: none"> <li>• Outputs</li> </ul>	4 byte
Hardware configuration	
Automatic encoding	Yes
<ul style="list-style-type: none"> <li>• Electronic coding element type F</li> </ul>	Yes
Digital inputs	
Number of digital inputs	8
Source/sink input	Yes; P-reading
Input characteristic curve in accordance with IEC 61131, type 1	Yes
Input voltage	
<ul style="list-style-type: none"> <li>• Rated value (DC)</li> </ul>	24 V
<ul style="list-style-type: none"> <li>• for signal "0"</li> </ul>	-30 to +5 V
<ul style="list-style-type: none"> <li>• for signal "1"</li> </ul>	+15 to +30 V
Input current	
<ul style="list-style-type: none"> <li>• for signal "1", typ.</li> </ul>	3.7 mA
Input delay (for rated value of input voltage)	
for standard inputs	
— parameterizable	Yes
— at "0" to "1", min.	0.4 ms
— at "0" to "1", max.	20 ms
— at "1" to "0", min.	0.4 ms
— at "1" to "0", max.	20 ms
for technological functions	
— parameterizable	No

<b>Cable length</b>	
• shielded, max.	1 000 m
• unshielded, max.	500 m
<b>Interrupts/diagnostics/status information</b>	
Diagnostics function	Yes
<b>Alarms</b>	
• Diagnostic alarm	Yes
• Hardware interrupt	No
<b>Diagnostics indication LED</b>	
• RUN LED	Yes; green LED
• ERROR LED	Yes; red LED
• Monitoring of the supply voltage (PWR-LED)	Yes; green PWR LED
• Channel status display	Yes; green LED
• for channel diagnostics	Yes; red LED
• for module diagnostics	Yes; green/red DIAG LED
<b>Potential separation</b>	
<b>Potential separation channels</b>	
• between the channels	No
• between the channels and backplane bus	Yes
• between the channels and the power supply of the electronics	No
<b>Isolation</b>	
Isolation tested with	707 V DC (type test)
<b>Standards, approvals, certificates</b>	
Suitable for safety functions	Yes
<b>Highest safety class achievable in safety mode</b>	
• Performance level according to ISO 13849-1	PLe
• SIL acc. to IEC 61508	SIL 3
<b>Probability of failure (for service life of 20 years and repair time of 100 hours)</b>	
— Low demand mode: PFDavg in accordance with SIL3	< 2.00E-05
— High demand/continuous mode: PFH in accordance with SIL3	< 1.00E-09 1/h
<b>Ambient conditions</b>	
<b>Ambient temperature during operation</b>	
• horizontal installation, min.	0 °C
• horizontal installation, max.	60 °C
• vertical installation, min.	0 °C
• vertical installation, max.	50 °C
<b>Altitude during operation relating to sea level</b>	

- Installation altitude above sea level, max.

4 000 m; Restrictions for installation altitudes > 2 000 m, see manual

#### Dimensions

Width	15 mm
Height	73 mm
Depth	58 mm

#### Weights

Weight, approx.	49 g
-----------------	------

**last modified:** 05/09/2020