

### product type designation



### PROFIBUS OBT

PROFIBUS OBT; opt. bus terminal for connection of a PROFIBUS nodes without integr. opt. interface to the opt. PROFIBUS DP; without Simplex plug.

transfer rate	
transfer rate / with PROFIBUS	9.6 kbit/s ... 12 Mbit/s
transfer rate / with PROFIBUS PA	45.45 kbit/s
interfaces	
number of electrical/optical connections / for network components or terminal equipment / maximum	3
number of electrical connections	
• for network components or terminal equipment	1
• for power supply	1
type of electrical connection	
• for network components or terminal equipment	9-pin Sub-D socket
• for power supply	3-pole terminal block
• for power supply and signaling contact	-
number of optical interfaces / for fiber optic cable	2
design of the optical interface / for fiber optic cable	Duplex port
optical data	
attenuation factor / of the FOC transmission link	
• for PCF FOC with 200/230 $\mu\text{m}$ / at 10 dB/km	3 dB
• for POF FOC with 980/1000 $\mu\text{m}$ / at 230 dB/km	13 dB
propagation delay [bit]	6.5 bit
connectable optical power relative to 1 mW	
• of the FOC transmission link / for PCF FOC with 200/230 $\mu\text{m}$ / at 10 dB/km	-16 dB
• of the FOC transmission link / for POF FOC with 980/1000 $\mu\text{m}$ / at 230 dB/km	-5.9 dB
optical sensitivity relating to 1 mW	
• of the FOC transmission link / for PCF FOC with 200/230 $\mu\text{m}$ / at 10 dB/km	-22 dB
• of the FOC transmission link / for POF FOC with 980/1000 $\mu\text{m}$ / at 230 dB/km	-20 dB
wavelength / of the optical interface / note	660 nm, POF/PCF
wire length	
• for PCF FOC with 200/230 $\mu\text{m}$ / at 10 dB/km / maximum	300 m
• for POF FOC with 980/1000 $\mu\text{m}$ / at 230 dB/km / maximum	50 m
supply voltage, current consumption, power loss	
type of voltage / of the supply voltage	DC
supply voltage / at DC / rated value	24 V
supply voltage / at DC	19.2 ... 28.8 V
ambient conditions	
ambient temperature	

<ul style="list-style-type: none"> <li>during operation</li> <li>during storage</li> <li>during transport</li> </ul>	<p>0 ... 60 °C</p> <p>-40 ... +70 °C</p> <p>-40 ... +70 °C</p>
<p>relative humidity</p> <ul style="list-style-type: none"> <li>at 25 °C / without condensation / during operation / maximum</li> </ul>	95 %
protection class IP	IP30
<b>design, dimensions and weights</b>	
design	compact
width	50.5 mm
height	138 mm
depth	78 mm
net weight	400 g
fastening method	
<ul style="list-style-type: none"> <li>35 mm DIN-rail mounting</li> <li>wall mounting</li> </ul>	<p>Yes</p> <p>Yes</p>
<b>product functions / redundancy</b>	
product function / ring redundancy	No
<b>standards, specifications, approvals</b>	
standard	
<ul style="list-style-type: none"> <li>for safety / from CSA and UL</li> <li>for emitted interference</li> <li>for interference immunity</li> </ul>	<p>UL 60950-1, CSA C22.2 Nr. 60950-1</p> <p>EN 61000-6-4 (Class A)</p> <p>EN 61000-6-2</p>
certificate of suitability	EN 61000-6-2, EN 61000-6-4
<ul style="list-style-type: none"> <li>CE marking</li> <li>C-Tick</li> </ul>	<p>Yes</p> <p>Yes</p>
Marine classification association	
<ul style="list-style-type: none"> <li>American Bureau of Shipping Europe Ltd. (ABS)</li> <li>French marine classification society (BV)</li> <li>Det Norske Veritas (DNV)</li> <li>Germanische Lloyd (GL)</li> <li>Lloyds Register of Shipping (LRS)</li> <li>Nippon Kaiji Kyokai (NK)</li> </ul>	<p>No</p> <p>No</p> <p>No</p> <p>No</p> <p>No</p> <p>No</p>
reference code	
<ul style="list-style-type: none"> <li>according to IEC 81346-2:2019</li> </ul>	KGA
product function / is supported / identification link	Yes; acc. to IEC 61406-1:2022
<b>standards, specifications, approvals / hazardous environments</b>	
certificate of suitability / CCC / for hazardous zone according to GB standard	No
<b>further information / internet links</b>	
internet link	
<ul style="list-style-type: none"> <li>to website: Selection guide for cables and connectors</li> <li>to web page: selection aid TIA Selection Tool</li> <li>to website: Industrial communication</li> <li>to web page: SiePortal</li> <li>to website: Image database</li> <li>to website: CAx-Download-Manager</li> <li>to website: Industry Online Support</li> </ul>	<p><a href="https://support.industry.siemens.com/cs/ww/en/view/109766358">https://support.industry.siemens.com/cs/ww/en/view/109766358</a></p> <p><a href="https://www.siemens.com/tstcloud">https://www.siemens.com/tstcloud</a></p> <p><a href="https://siemens.com/industrial-communication">https://siemens.com/industrial-communication</a></p> <p><a href="https://sieportal.siemens.com/">https://sieportal.siemens.com/</a></p> <p><a href="https://www.automation.siemens.com/bilddb">https://www.automation.siemens.com/bilddb</a></p> <p><a href="https://www.siemens.com/cax">https://www.siemens.com/cax</a></p> <p><a href="https://support.industry.siemens.com">https://support.industry.siemens.com</a></p>
<b>security information</b>	
security information	<p>Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit <a href="http://www.siemens.com/cybersecurity-industry">www.siemens.com/cybersecurity-industry</a>. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase</p>

customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under <https://www.siemens.com/cert.> (V4.7)

Approvals / Certificates

General Product Approval



[Declaration of Conformity](#)



[China RoHS](#)

General Product Approval

For use in hazardous locations

Maritime application



[FM](#)

[CCC-Ex](#)



Maritime application



[NK / Nippon Kaiji Kyokai](#)



last modified:

2/18/2025