



Siemens Low Voltage Circuit Protection General Duty Safety Switch. 2-Pole or 3-Pole Non-Fused in a type 1 enclosure (indoor). Rated 240VAC (100A). Horse power: 1-PH 2-W (15), 3-PH 3-W (30), 250VDC (20). Special features: service entrance labeled suitable for 3-PH motor loads.

General technical data	
mechanical service life (operating cycles) typical	10000
fastening method	SURFACE
product function note	
number of poles	3
suitability for operation	DISCONNECTING MEAN FOR SERVICE ENTRANCE / LOADS
Electricity	
ampacity	100 A
Environmental conditions	
ambient temperature during operation maximum	85 °C
ambient temperature during operation minimum	-29 °C
Model	
product brand name	SIEMENS
product sub brand name	VBII
product type designation	GENERAL DUTY SWITCH
type of electrical connection	MECHANICAL LUGS
Mechanical Design	
design of the housing	TYPE 1
design of the actuating element	SINGLE THROW
material	STEEL
General product approval	
certificate of suitability	UL98

last modified:

7/18/2024 

