



DATE	REV	ECN	APP'D. BY
10/25/19	A0	–	JME
12/04/19	A1	11483	ADB



PART NUMBER KEY



O/A Length Tolerance:

Metric	
0 ~ 200mm	±10mm
201 ~ 1000mm	±20mm
1001 ~ 1500mm	±25mm
1501 ~ 2100mm	±30mm
>2100mm	±40mm
Imperial	
0 ~ 1ft	±0.5in
2ft ~ 3ft	±0.75in
4ft ~ 7ft	±1.0in
> 7ft	±1.5in

NOTES:

1. EACH CABLE ASSEMBLY INDIVIDUALLY BAGGED
2. WIRE CONSTRUCTION: 28 AWG WIRE, FLAT TELEPHONE, OD 0.01 x 0.2", SILVER/GREY INSULATION
3. CONNECTOR P1: 6P6C MODULAR PLUG, GOLD FLASH ON CONTACTS
4. CONNECTOR P2: 6P6C MODULAR PLUG, GOLD FLASH ON CONTACTS
5. VOLTAGE RATING: 300 V
6. CONDUCTOR RESISTANCE: 8 Ω
7. INSULATION RESISTANCE: 5M Ω

WIRING MAP

P1	P2	
1	6	BLUE
2	5	YELLOW
3	4	GREEN
4	3	RED
5	2	BLACK
6	1	WHITE

TYPICAL PART NUMBERS	
PART NUMBER	LENGTH FEET [METERS]
BC-66RS007F	7 [2.13]
BC-66RS014F	14 [4.27]
BC-66RS025F	25 [7.62]
FOR PART NUMBERS NOT SHOWN FOLLOW PART NUMBER KEY FORMAT	



THIRD ANGLE PROJECTION

DO NOT SCALE DRAWING
DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS: INCHES [METRIC]
UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE ±.005 [0.13]
ANGLES ARE ± 1°
SHEET NO. 1 OF 1

206 Van Vorst Street
Jersey City, NJ 07302
+1 201 432 0463
<http://www.belfuse.com>

TITLE: RJ12 PATCHCORD CABLE WITH 6 POSITION, 6 CONTACT
MODULAR PLUGS (REVERSE)

DRN BY: BTS
DATE 10/19/19

APPD BY: JME
DATE 10/25/19

DWG NO. CT999206
REV. A1

THIS DRAWING AND THE SUBJECT MATTER SHOWN THEREON ARE CONFIDENTIAL AND THE PROPRIETARY PROPERTY OF BEL FUSE, INC. AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT PRIOR WRITTEN CONSENT OF BEL FUSE, INC.