

1SNL906750R0000 ✓ ACTIVE



TE Internal #: 1SNL906750R0000


Terminal Block & Strip Conducting Accessories, Jumper Bar, 50

Pole, Black, Product Spacing .236 in [6 mm], -55 – 110 °C [-67 – 230 °

F]

[View on TE.com >](#)

Connectors > Terminal Blocks & Strips > Terminal Block & Strip Accessories > Terminal Block & Strip Conducting Accessories



Conducting Accessory Type: **Jumper Bar**

Number of Poles: **50**

Primary Product Color: **Black**

Product Spacing: **6 mm [.236 in]**

Operating Temperature Range: **-55 – 110 °C [-67 – 230 °F]**

Features

Product Type Features

Conducting Accessory Type	Jumper Bar
---------------------------	------------

Configuration Features

Number of Poles	50
-----------------	----

Electrical Characteristics

Current Rating (IEC)	24 A
----------------------	------

Body Features

Plastic & Resin Material Type	PVC
Product Weight	25.5 g[.899 oz]
Primary Product Color	Black

Dimensions

Product Depth	22 mm[.787 in]
Product Width	7.14 mm[.281 in]
Product Length	297.8 mm[11.724 in]
Product Height	21.83 mm[.859 in]

Product Spacing	6 mm [.236 in]
-----------------	----------------

Usage Conditions

Storage Temperature Range	-55 – 110 °C [-67 – 230 °F]
---------------------------	-----------------------------

Installation Temperature Range	-5 – 40 °C [23 – 104 °F]
--------------------------------	--------------------------

Operating Temperature Range	-55 – 110 °C [-67 – 230 °F]
-----------------------------	-----------------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JAN 2020 (205) SVHC > Threshold: Not Yet Reviewed
--	---

Halogen Content	Not Yet Reviewed for halogen content
-----------------	--------------------------------------

Solder Process Capability	Not reviewed for solder process capability
---------------------------	--

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought



Documents

[CAD Files](#)

[3D PDF](#)

[3D](#)

[Customer View Model](#)

[ENG_CVM_CVM_1SNL906750R0000_B.2d_dxf.zip](#)

English

[Customer View Model](#)

[ENG_CVM_CVM_1SNL906750R0000_B.3d_igs.zip](#)

English

1SNL906750R0000

Terminal Block & Strip Conducting Accessories, Jumper Bar, 50 Pole, Black, Product Spacing .236 in [6 mm], -55 – 110 °C [-67 – 230 °F]



Customer View Model

[ENG_CVM_CVM_1SNL906750R0000_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SNACOMPACT TERMINAL BLOCKS SCREW CLAMP TECHNOLOGY](#)

English

[LJB6-50](#)

English