

9007DA9M

9007C limit switch lever - zinc - fixed length - outside ball bearing roller



Main

| | |
|-----------------------------|---|
| Range of product | 9007 |
| Series name | Heavy duty |
| Product or component type | Limit switch lever |
| Device short name | 9007C |
| Associated head | 9007A 9007B 9007C 9007N 9007T10 9007T5 |
| Associated complete product | 9007AW 9007C |
| Movement of operating head | Rotary |
| Type of operator | Cast zinc spring return 360° adjustable roller lever length: 2.5 in - offset: - ball bearing roller to pass over switch cover |
| Type of roller | 1 steel outside roller (convertible) diameter: 0.69 in - width: 0.25 in |
| Type of approach | Lateral approach |
| Positive opening | Without |

Complementary

| | |
|------------------|------------|
| Switch actuation | By 30° cam |
| Product weight | 0.1 lb(US) |

Environment

| | |
|---------------------------------------|----------------------|
| Ambient air temperature for operation | -20...185 °F |
| Ambient air temperature for storage | -20...185 °F |
| Environmental characteristic | Standard environment |

Offer Sustainability

| | |
|----------------------------------|--|
| Sustainable offer status | Not Green Premium product |
| RoHS | Will be Compliant on 3Q2014 Will be Compliant on 3Q2014 |
| REACH | Reference not containing SVHC above the threshold |
| Product environmental profile | Available |
| Product end of life instructions | Need no specific recycling operations |

Contractual warranty

| | |
|--------|-----------|
| Period | 18 months |
|--------|-----------|

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.