

Wire-wound Chip Power Inductors (BR series)

BRL2012T150M



■ Features

- Item Summary
15 μ H \pm 20%, 0.22A, 0805/2012 (EIA/JIS)
- Lifecycle Stage
Mass Production
- Standard packaging quantity (minimum)
Taping Embossed 3000pcs

■ Products characteristics table

Inductance	15 μ H \pm 20 %
Case Size (EIA/JIS)	0805/2012
Rated Current (max)	0.22 A
Saturation Current (max)	0.22 A
Temperature Rise Current (max)	0.3 A
DC Resistance (typ)	1 Ω
DC Resistance (max)	1.3 Ω
LQ Measuring Frequency	2.52 MHz
Self Resonant Frequency (min)	15 MHz
Operating Temp. Range	-40 to +105 $^{\circ}$ C (Including-self-generated heat)
RoHS2 Compliance (10 subst.)	Yes
REACH Compliance (163 subst.)	Yes
Soldering	Reflow

■ External Dimensions

Dimension L	2.0 \pm 0.2 mm
Dimension W	1.25 \pm 0.2 mm
Dimension T	Max 1.0 mm
Dimension e	0.5 \pm 0.2 mm

2016.02.15

The data is reference only. Electrical characteristics vary depending on environment or measurement condition.
 TAIYO YUDEN reserves the right to make change to the Date at any time without notice.
 Before making final selection, please check product specification.