



Representative

Catalog Number: F10721
Product ID: 7TAI029620R0084
UPC Number: 78621082967
EAN Number: 05414363151043
Status: Active

Non-Insulated Tubular Ring Terminal, Length 1.42 Inches, Width .62 Inches, Bolt Hole 5/16 Inch, Wire Range 4/4AN, Copper, Tin Plated

- These non-insulated ring terminals are made of electrolytic copper for high conductivity.
- They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire).

UNSPSC Specifications

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Brand Name	Sta-Kon
Type	Ring Terminal
Special Features	These non-insulated ring terminals are made of electrolytic copper for high conductivity. They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire).
Wire Size	4
Voltage Rating	600V
Material	Copper
Color	Metallic

ETIM Specifications

ETIM	EC001051 Tube cable lug for copper conductors
Connecting angle	Straight
Flange shape	Ring shape
Slender flange model	N
Insulated	N
Material	Copper
Surface protection	Tinned
Number of fixing holes	1

Packaging

Inner Quantity	100
Inner Dimensions (inches)	3.5x3x3
Outer Quantity	1000
Outer Dimensions (inches)	16.4x7.9x3.7
Weight Uom	2.5 lbs. per 100

Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-000168

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com