



Actual

Catalog Number: 210214MT
Product ID: 7TAI029010R0006
UPC Number: 78621083926
EAN Number: 05414363111733
Status: Active

Insulation Piercing Magnet Wire Modular Connector, Length Between Teeth .19 Inches, Length .63 Inches, Width .63 Inches, Wire Range #13 AWG - #5 AWG 20,000 Circular Mil Area - 105,000 Circular Mil Area, Copper Alloy, Tin Plated

- Designed to penetrate magnet wire insulation during application, eliminating the need for stripping, brazing, welding or other methods of joining magnet wire.
- For aluminum to copper, aluminum to aluminum or copper to copper magnet wire connections.

North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Brand Name	Dragon Tooth
Type	Modular Connectors
Special Features	Designed to penetrate magnet wire insulation during application, eliminating the need for stripping, brazing, welding or other methods of joining magnet wire.
Application	For aluminum to copper, aluminum to aluminum or copper to copper magnet wire connections.
Standard	UL E9809
Material	Copper

European Specifications (ETIM)

ETIM	EC001059 Crimp splices for copper conductor
AWG-range	13-5
Model	Standard version
Sleeve form	Short
Suitable for solid cores	N
Useful for stranded conductors	N
Suitable for fine strand conductors	N
Suitable for insulated varnish	Y
Suitable for round conductors	Y
Suitable for flat conductors	Y
Material	Copper
Surface protection	Tinned
Insulation	None
Voltage row	Up to 600 V
Type of connection	End connector
Oil stop/centre bar	N

Packaging

Outer Quantity	250
Outer Dimensions (inches)	10x7.25x4.25
Weight Uom	4.06 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US Available on Website

For further technical assistance, please contact us...

Memphis, TN 38120
www.tnb.com

860 Ridge Lake Blvd.
Memphis, TN 38120

Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com