



Representative



Family

Catalog Number: BGG-56
Product ID: 7TAA292860R0001
UPC Number: 78620994582
EAN Number: 07630030209314
Status: Active

PMAGRIP Black Straight Flange, Material - Polyamide 6, Fits to Conduit Size NW - 56

- Very high impact resistance
- Vibration-proof connection to PMAFLEX conduits
- High conduit pull-out strength
- Selectable flange seal
- Very good chemical properties
- Self-extinguishing
- Free from halogens and cadmium
- Using the enclosed seals an ingress protection rating of up to IP65 can be achieved

North American Specifications (UNSPSC)

UNSPSC	31162906 Hose or pipe clamps
IGCC	3064 Hose or pipe clamps
Brand Name	PMA
Type	Flexible Conduits & Fittings
Application	For Cable Protection Systems In a Wide Range of Industrial Applications
Material	Polyamide/Nylon 6
Size	NW56
Color	Black

European Specifications (ETIM)

ETIM	EC001176 Screw connection for corrugated plastic hose
Nominal diameter	68mm
Degree of protection (IP)	IP65
Model	Straight
Revolving thread	N
Construction type	Flange
Type of connection	Snap connection
Thread connection size	None
Thread material	Polyamide
Thread length	0mm
Total length	60mm
Material	Polyamide
Material sealing	Other
Colour	Black
Approved in combination with protective conduit CSA	N
Approved in combination with protective conduit UR	Y
Approved in combination with protective conduit DIN EN 61386-23	N
Approved in combination with protective conduit Lloyd's Register	N
Operating temperature	-40 - +105°C

Packaging

Inner Quantity	10
Outer Quantity	100
Outer Dimensions (inches)	15.748x15.748x14.173
Weight Uom	0.2 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet Canada Available on Website

Header

3D Model Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
860 Ridge Lake Blvd.
Memphis, TN 38120
www.tnb.com

T&B Technical Support
MS 3B-50
860 Ridge Lake Blvd.
Memphis, TN 38120

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com