



Russellstoll[®]

MaxGuard Interconnection Systems

T&B Catalog Number:

UPC Number:

Status:

Description:

DF1404FP000

70891715145

Active

MaxGuard Female Connector, 100 Amp, 3 Pole 4 Wire, 30 480V, 60Hz

Features

Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight").

Two optional pilot/control pins for contractors, load monitor circuits, shunt trip or any other communication functions you need.

Center ground contacts: make FIRST, break LAST
All receptacles and connectors have a gated rotating disk on the face of the interior, engaged on insertion.



Application

Convention centers and arenas

For use in applications where outdoor, severe or high abuse environments exist.

Convention centers and arenas

General

Style	Load Breaking Female Connector
Material	Copper Free, Cast Aluminum, Epoxy Powder-Coated Housing
Material_1	Standard Neoprene O-ring interior components
Frequency	60 Hz
Amperage	100 Amp
Pole/Wire	3P/4W
System	Heavy Industrial & Marine

Dimension Information

Overall Dimensions	Available on Website
--------------------	----------------------

Specifications

Voltage	3 Phase 480 Volts AC
Engineering Specifications	Available on Website

Packaging

Package in Units	1
T&B Sold in UOM	Each
T&B Weight Per UOM	6.65 lbs. Each

Application Support

Overview	Available on Website
Russellstoll Application Guide	Available on Website

For further technical assistance, please contact us...

8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com