



MEAS | MEAS PT101

TE Internal #: 04-0760-0797

TE Internal Description: PT101-0075-113-2120

VOLTAGE DIVIDER STRING POT

[View on TE.com >](#)

Sensors > Position Sensors > Potentiometer Sensors > Cable Actuated Position Sensors > VOLTAGE DIVIDER STRING POT



Position Sensor Product Type: **Industrial String Potentiometer**

Full Stroke Range: 1905 mm [75 in]

Output Signal Type: **Voltage Divider (Potentiometric)**

Accuracy: $\pm 1\%$ of FS

Repeatability: $.02\%$ of FS

[All VOLTAGE DIVIDER STRING POT \(421\)](#)

Features

Product Type Features

Position Sensor Product Type	Industrial String Potentiometer
------------------------------	---------------------------------

Body Features

Case Material	Aluminum
---------------	----------

Dimensions

Full Stroke Range	1905 mm[75 in]
-------------------	----------------

Usage Conditions

Accuracy	$\pm 1\%$ of FS
Operating Temperature Range	-40 – 90 °C[-40 – 194 °F]

Operation/Application

Output Signal Type	Voltage Divider (Potentiometric)
--------------------	----------------------------------

Industry Standards

IP Rating	IP50
-----------	------

Other

Encoder Drive	No
Repeatability	$.02\%$ of FS
Measuring Cable	.019 Inch Dia Nylon-Coated Stainless Steel

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	<p>Current ECHA Candidate List: JUNE 2025 (250)</p> <p>Candidate List Declared Against: JAN 2025 (247)</p> <p>SVHC > Threshold: Pb (.3% in Component Part)</p> <p>Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.</p>
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | [MEAS PT101](#)



[Cable Actuated Position Sensors\(421\)](#)

Documents

[Datasheets & Catalog Pages](#)



PT101

English