



Connectors > Terminal Blocks & Strips > Modular Terminal Blocks



Block Function: **Component Holder**

Modular Terminal Block Product Type: **PI-Spring Terminal Block**

Primary Product Color: **Gray**

Product Spacing: **5.2 mm [.205 in]**

Number of Positions: **4**

Features

Product Type Features

Modular Terminal Block Product Type	PI-Spring Terminal Block
-------------------------------------	--------------------------

Configuration Features

Number of Levels	2
Gauge Type	A3-B3
Number of Circuits	2
Block Function	Component Holder
Number of Positions	4

Electrical Characteristics

Power Loss	1.6 W
Operating Voltage Rating (UL & CSA) (Max) - Main Circuit	600 V
Current Rating (IEC)	24 A
Current Rating (UL)	20 A
Current Rating (CSA)	20 A
Voltage Rating (IEC)	800 V
Voltage Rating (CSA)	600 V

Body Features

Product Weight	11.2 g[.441 oz]
----------------	-----------------



Primary Product Color

Gray

Mechanical Attachment

DIN Rail Mounting Type	TH35-15, TH35-7.5
Connector Mounting Type	DIN Rail

Housing Features

Housing Material	Polyamide
------------------	-----------

Dimensions

Main Circuit Capacity - Twin Ferrule per Spring Clamp	26 – 20 AWG
Product Depth	60.2 mm
Tool Size	3.5 mm[.138 in]
Wire Stripping Length	11 mm[.433 in]
Main Circuit Capacity - 1 Rigid Stranded Conductor per Spring Clamp	26 – 12 AWG
Main Circuit Capacity - 1 Non-Insulated Ferrule per Spring Clamp	26 – 14 AWG
Main Circuit Capacity - 1 Insulated Ferrule per Spring Clamp	26 – 14 AWG
Main Circuit Capacity - 1 Flexible Conductor per Spring Clamp	.22 – 2.5 mm²
Product Length	60.2 mm[2.58 in]
Product Height	78.5 mm
Product Spacing	5.2 mm[.205 in]

Usage Conditions

Installation Temperature Range	-5 – 40 °C[23 – 104 °F]
Operating Temperature Range	-55 – 110 °C[-67 – 230 °F]

Industry Standards

IP Rating	IP20
UL Flammability Rating	UL 94V-0

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量超出标准 Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	



Current ECHA Candidate List: JUNE 2025 (250)

Candidate List Declared Against: JUNE 2025 (250)

SVHC > Threshold:

Pb (92.5% in Component Part)

Article Safe Usage Statements:
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 1SNK149999R0000
MC512PA



TE Part # 1SNK705960R0000
EK2.5-D2



TE Part # 1SNK900609R0000
PROCAP5



TE Part # 1SNA168500R1200
PR4



TE Part # 1SNK905350R0000
JB5-50



TE Part # 1SNK900200R0000
TC5




TE Part # 1SNK905310R0000
JB5-10



TE Part # 1SNK905304R0000
JB5-4

1SNK705213R0000

PI-Spring Terminal Block, Component Holder, Gray, 5.2 mm [.205 in] Spacing, 4 Position, DIN Rail, -55 – 110 °C [-67 – 230 °F], ENTRELEC SNK



TE Part # 1SNA173220R0500
PR30



TE Part # 1SNK905305R0000
JB5-5



TE Part # 1SNK900602R0000
SHB



TE Part # 1SNK900611R0000
UMH




TE Part # 1SNK905303R0000
JB5-3




TE Part # 1SNK140000R0000
MC512




TE Part # 1SNK905302R0000
JB5-2



TE Part # 1SNA178529R0400
PR50



TE Part # 1SNK140004R0000
MC512-YL



TE Part # 1SNA174300R1700
PR3.Z2




TE Part # 1SNK900203R0000
TP2



TE Part # 1SNK900403R0000
PG5-R2


Also in the Series | ENTRELEC SNK



Modular Terminal Blocks(319)



Terminal Block & Strip Conducting
Accessories(67)



Terminal Block & Strip Insulating
Accessories(31)

Customers Also Bought



TE Part #1SNK705912R0000
EK2.5-4P



TE Part #1SNK705152R0000
ZK2.5-PE-4P




TE Part #1SNK708151R0000
ZK6-PE-3P



TE Part #1SNK147011R0000
MC512PA 1 (x100) Horizontal

1SNK705213R0000

PI-Spring Terminal Block, Component Holder, Gray, 5.2 mm [.205 in] Spacing, 4 Position, DIN Rail, -55 – 110 °C [-67 – 230 °F], ENTRELEC SNK



Documents

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1SNK705213R0000_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1SNK705213R0000_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1SNK705213R0000_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[ENTRELEC Terminal Block - Master Catalog](#)

[ENTRELEC Terminal Block - Master Catalog](#)

English

[ZK2.5-D-CH-UD](#)

English

[SNK SERIES TERMINAL BLOCKS](#)

English

[ENTRELEC Terminal Blocks Catalogue \(RUS\)](#)

Agency Approvals

[Bureau Veritas Marine and Offshore Certificate](#)

1SNK705213R0000

PI-Spring Terminal Block, Component Holder, Gray, 5.2 mm [.205 in] Spacing, 4
Position, DIN Rail, -55 – 110 °C [-67 – 230 °F], ENTRELEC SNK



English