PT5DC-80-S47-FR-10Z-M6M ✔ ACTIVE

MEAS | MEAS PT5

TE Internal #: 04-1006-0571

TE Internal Description: PT5DC-80-S47-FR-10Z-M6M
VOLTAGE OUT INDUSTRIAL STRING POT

View on TE.com >

Sensors > Position Sensors > Potentiometer Sensors > Cable Actuated Position Sensors > VOLTAGE OUT INDUSTRIAL STRING POT



Position Sensor Product Type: **Industrial String Potentiometer**

Full Stroke Range: **2032 mm [80 in]**

Output Signal Type: **10 – 0 VDC**

Accuracy: **±.25 % of FS**

Repeatability: **.02 % of FS**

All VOLTAGE OUT INDUSTRIAL STRING POT (311)

Features

Product Type Features

Position Sensor Product Type	Industrial String Potentiometer

Body Features

Case Material	Aluminum

Dimensions

Full Stroke Range	2032 mm[80 in]

Usage Conditions

Accuracy	±.25 % of FS
Operating Temperature Range	-40 – 90 °C[-40 – 194 °F]

Operation/Application

Output Signal Type	10 – 0 VDC

Industry Standards

IP Rating	IP65

Other

Encoder Drive	No
Repeatability	.02 % of FS
Measuring Cable	.047 Inch Dia Stainless Steel

PT5DC-80-S47-FR-10Z-M6M

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量超出标准 Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked.Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles'(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Also in the Series | MEAS PT5



Cable Actuated Position Sensors(1643)

Customers Also Bought

PT5DC-80-S47-FR-10Z-M6M



TE Part #2-1393127-6
PRD-11AY0-120=PRD

Documents

Datasheets & Catalog Pages

PT5DC

English