



Flexible Conduits & Fittings

T&B Catalog Number:

VAMG-23B.50

UPC Number:

78620997652

Status:

Active

Description:

Heavy wall, flexible black conduit. (VAM) Material - polyamide 6, conduit size NW - 23.

Application

Machine
Renewable Energy
Rail
In passenger areas of railway vehicles
Public buildings to include hospitals, hotels, airports, train and subway stations and shopping centers

Characteristics

Good resistance to ultra violet rays and weathering
High impact and compression strength
High stiffness
Outstanding self-extinguishing characteristics
Minimal development of smoke and gases
Free from halogens and cadmium

General

Material	Polyamide 6
Material-Conduit Core	Non-Metallic
Color	Black
System	PMAFLEX
Compatible With	PMAFIX Pro, PMAFIX, PMA Smart Line

Dimension Information

Conduit Size (inches)	3/4
Conduit Size NW (mm)	23
Conduit Size Metric (mm)	25
Outside Diameter (inches)	1.12
Inside Diameter (mm)	22
Outside Diameter (mm)	28.5
Static Radius (mm)	50
Rec. Fitting Thread-Metric	M25 x 1.5
Rec. Fitting Thread-PG	21

Technical Information

Temperature Range-Continuous (Celsius)	-40 to +105
Temperature-Short-Term (Celsius)	160
Fatigue Life	Low
Technical Data Sheet	Available on Website
Chemical Resistance Chart	Available on Website

Packaging

T&B Order Multiple	1
T&B Inner Pack	1
Package in Units	10
T&B Sold in UOM	Each
T&B Weight Per UOM	14.61 lbs. Each

Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com