



Actual

**Catalog Number:** CKMU  
**Product ID:** 7TAA002500R0006  
**UPC Number:** 04226900465  
**Status:** A

Single Gang While-In-Use Universal Medium Horizontal Cover, 3-1/4 Inch Internal Depth, Silver, Aluminum, For use with Duplex, GFI, Single Receptacle, and Switch

- Combination box or device-mounting design provides flexibility in installation.
- NEMA 3R rating ensures protection against falling rain, sleet and external ice formation when used with appropriate device boxes
- Clear UL and CSA markings speed approval by inspectors
- Wide range of cover depths and receptacle configurations accommodate almost every common plug and cord size when combined with included adapter plates
- Combination box or device mounting design provides flexibility in installation

### North American Specifications (UNSPSC)

UNSPSC	39121304 Electrical box covers
IGCC	4425 Electrical box covers
Brand Name	Red Dot
Type	While-In-Use-Weatherproof Covers
Special Features	Die-cast metal construction provides long-lasting durability
Application	Residential-Holiday and landscape lighting, wells and sump pumps, sprinkler systems, plug-in timers, garages and patios
Standard	UL E28688
Material	Aluminum Die Cast
Finish	Powder-coated
Color	Silver

### European Specifications (ETIM)

ETIM	EC002656 Cover for box/housing for built-in mounting in the wall/ceiling
Depth	82.55mm
Shape	Rectangular
Type of fastening	Screw cover
Model	Mounting cover
Material	Other
Colour	Other
With screws	N

### Packaging

Outer Quantity	3
Outer Dimensions (inches)	11.625x5.75x6.25
Weight Uom	0.82 lbs. Each

### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Instruction Sheet	TA04207-TB2
Marketing Brochure US	Available on Website
Catalog US	Available on Website

**For further technical assistance, please contact us...**

Memphis, TN 38120  
[www.tnb.com](http://www.tnb.com)

860 Ridge Lake Blvd.  
Memphis, TN 38120

Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)