



Representative

**Catalog Number:** NC12/100M  
**Product ID:** 7TCA298000R0209  
**UPC Number:** 78621014688  
**EAN Number:** 05020963023033  
**Status:** Active

Standard Weight, General Purpose Conduit, NC Size 12/NW Size 10, Outside Diameter 13.0mm, Inside Diameter 9.9mm, Static Bend Radius 20mm, High Flexibility and Fatigue Life, IP40 Rating, Polyamide 6, Reel Length 100 Meters, Black

### North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5540 Flexible Non-Metallic Conduit
Brand Name	Harnessflex
Type	Standard Weight Conduit
Application	Extensively Used in Harnesses on HGV and off Road Vehicles Applications Where Superior Protection Against Impact and Mechanical Shock is Preferred. The Conduit is Used for Both Chassis and Engine Applications and Can Be Used in a Wide Range of Temperatures
Standard	ADR Approved, RoHS, Conforms with End of Life Vehicle Directive (ELV)EU200/53/EC
Trade Size	NC12/NW10
Outside Diameter	13.0mm
Inside Diameter	9.9mm
Length	100 m
Radius	Static Bend Radius 20mm
Flexibility	Very High
Material	Polyamide/Nylon 6
Color	Black

### European Specifications (ETIM)

ETIM	EC001175 Corrugated plastic hose
Nominal diameter	12mm
Nominal size in inch	5/16 inch
Outer diameter	13mm
Inner diameter	9.9mm
Material	Polyamide 6
Operating temperature	-40-+120°C
Degree of protection (IP)	IP40
Fire resistance in accordance with UL94	HB
UV resistant	Y
Colour	Black
Sheathing material	Not sheathed
Bending strength	Flexible
Lengthwise slotted	N
Halogen free	Y

### Packaging

Inner Quantity	1
Inner Dimensions (inches)	17x37x17
Outer Quantity	10
Outer Dimensions (inches)	17x37x17
Weight Uom	5.29 lbs. Each

### Header

3D Model	Available on Website
----------	----------------------

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
860 Ridge Lake Blvd.  
Memphis, TN 38120  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
860 Ridge Lake Blvd.  
Memphis, TN 38120

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)