

AST4000F06400P1Z1000 × OBSOLETE

AST | AST4000

TE Internal #: 11192061-00

TE Internal Description: 6400 PSI, 7/16-20UNF Male, 0.5-4.5V

4-20mA / Voltage Pressure Transducer

[View on TE.com >](#)



Sensors > Pressure Sensors > Pressure Transducers > 4-20mA / Voltage Pressure Transducer



Pressure Sensor Type: **Industrial Pressure Transducer**

Pressure Type: **Gauge**

Output Signal Type: **.5 – 4.5 V**

Pressure: **441.26 bar [6400 psi]**

Supply Voltage Range: **10 – 28 V**

[All 4-20mA / Voltage Pressure Transducer \(53\)](#)

Features

Product Type Features

Pressure Sensor Type Industrial Pressure Transducer

Pressure Type Gauge

Configuration Features

Electrical Connection Deutsch DT04-3P

Electrical Characteristics

Supply Voltage Range 10 – 28 V

Body Features

Port Material 316L

Usage Conditions

Pressure 441.26 bar[6400 psi]

Operation/Application

Output Signal Type .5 – 4.5 V

Proof Pressure Range 2X, Min

Pressure Accuracy ±0.5% FSO

Industry Standards

Compatible With Agency/Standards Products UL



Other

Sensor Options	No Option
Port Fitting	7/16-20 UNF Male

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量超出标准 Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Also in the Series | **AST4000**



[Industrial Pressure Transducers\(53\)](#)



[Pressure Transducers\(53\)](#)

Customers Also Bought



Documents

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_11192061-00_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_11192061-00_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_11192061-00_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[AST4000 Datasheet](#)

English