



# Dragon Tooth®

**Splices**

**T&B Catalog Number:**

204210S

**UPC Number:**

78621086775

**Status:**

Active

**Description:**

Connector Insulation Piercing Splices .69x.53x.25, 10,380 - 52,480 CMA

**Dimension Information**

E* (inches)	.25
A (inches)	.69
D (inches)	.53

**Specifications**

Circular Mil Area	10,380 - 52,480
Rectangular Wire Range Thickness (inches)	.10 - .16
Rectangular Wire Range Width (inches)	.10 - .26
Round Wire Range AWG	12(b) - 2(e)

**Tooling**

Connector & Tooling Chart	Available on Website
---------------------------	----------------------

**Packaging**

T&B Order Multiple	100
T&B Inner Pack	100
Package in Units	500
T&B Sold in UOM	Each
T&B Weight Per UOM	2.03 lbs. per 100

**Application Support**

Product Selector	DT_prod_selector_splices
T&B Instruction Sheets	ta00193-tb2
Overview	Available on Website

**Notes**

*Note	Reference dimension (crimped height). See installing die illustration for gauging.
**Note	Not recommended for aluminum magnet wire finer than 21 gauge or 0.4 mm <sup>2</sup> . (a) Four wires max. (b) Six wires max. (c) Six wires max. each barrel (d) Conductors heavier than 6 AWG or 13 mm <sup>2</sup> require special dies. Contact Thomas & Betts for assistance. (e) Crimping dies may not bottom. Connector height will depend on number and size of wires in barrel. Pump must deliver 9800 psi minimum.
	Wire sizes and combinations shown have been tested to and meet or exceed Thomas & Betts specifications. Connectors may be suitable for other wire sizes or combinations. Thomas & Betts sells these connectors with the understanding that the user will perform necessary tests to determine their suitability for the intended purpose.

## Certifications

RoHS Compliance	Yes
-----------------	-----

### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)