






VLF252012MT-2R2M

Applications		Commercial Grade
Feature		Wire Wound
		Magnetic Shield
		Ferrite Core
Series	VLF-M Series / VLF252012MT Type	
Status	Production	



Size	
Length(L)	2.50mm +/-0.20mm
Width(W)	2.00mm +/-0.20mm
Thickness(T)	1.20mm Max.
Recommended Land Pattern (A)	0.75mm Nom.
Recommended Land Pattern (B)	0.60mm Nom.
Recommended Land Pattern (C)	1.30mm Nom.


Electrical Characteristics	
Inductance	2.2uH +/-20% at 1MHz
Rated Current (L Change) [Typ.]	1.04A (30% Down)
Rated Current (L Change) [Max.]	940mA (30% Down)
Rated Current (Temperature Rise) [Typ.]	1.67A (40degC Rise)
DC Resistance [Nom.]	90mΩ
DC Resistance [Max.]	100mΩ

Other	
Operating Temp. Range (Including Self-Temp. Rise)	-40 to 105degC
Soldering Method	Reflow
AEC Q200	No
Packing	Blister (Plastic)Taping [180mm Reel]
Package Quantity	2000Pcs Min.
Weight	0.021g


•This PDF document was created based on the data listed on the TDK Corporation website.
 •All specifications are subject to change without notice.

VLF252012MT-2R2M


Characteristic Graphs (This is reference data, and does not guarantee the product's characteristics.)




VLF252012MT-2R2M



VLF252012MT-2R2M



VLF252012MT-2R2M





VLF252012MT-2R2M

•This PDF document was created based on the data listed on the TDK Corporation website.
 •All specifications are subject to change without notice.


VLF252012MT-2R2M

Characteristic Graphs (This is reference data, and does not guarantee the product's characteristics.)



VLF252012MT-2R2M(DC = 0A)

VLF252012MT-2R2M(DC = 0.47A)



- This PDF document was created based on the data listed on the TDK Corporation website.
- All specifications are subject to change without notice.