



MEAS | MEAS PT1

TE Internal #: 04-1103-0177

TE Internal Description: PT1A-40-UP-500-M6

VOLTAGE DIVIDER PT1 STRING POT

[View on TE.com >](#)

Sensors > Position Sensors > Potentiometer Sensors > Cable Actuated Position Sensors > VOLTAGE DIVIDER PT1 STRING POT



Position Sensor Product Type: **Instrument Grade Potentiometer, Miniature String Potentiometer**

Full Stroke Range: **1016 mm [ 40 in ]**

Output Signal Type: **Voltage Divider (Potentiometric)**

Accuracy: **±.1 % of FS**

Repeatability: **.02 % of FS**

[All VOLTAGE DIVIDER PT1 STRING POT \(447\)](#)

## Features

### Product Type Features

Position Sensor Product Type	Instrument Grade Potentiometer, Miniature String Potentiometer
------------------------------	--

### Body Features

Case Material	Aluminum + Polycarbonate
---------------	--------------------------

### Dimensions

Full Stroke Range	1016 mm[40 in]
-------------------	----------------

### Usage Conditions

Accuracy	±.1 % of FS
Operating Temperature Range	-40 – 90 °C[-40 – 200 °F]

### Operation/Application

Output Signal Type	Voltage Divider (Potentiometric)
--------------------	----------------------------------

### Industry Standards

IP Rating	IP65
-----------	------

### Other

Encoder Drive	No
Repeatability	.02 % of FS

Measuring Cable

.019 Inch Dia Nylon-Coated Stainless Steel

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU

Compliant with Exemptions

EU ELV Directive 2000/53/EC

Not Yet Reviewed

China RoHS 2 Directive MIIT Order No 32, 2016

有害物质含量超出标准 Restricted  
Substance(s) Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2025 (250)

Candidate List Declared Against: JUNE 2025 (250)

SVHC &gt; Threshold:

Pb (3.5% in Component Part)

**Article Safe Usage Statements:**

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Not Yet Reviewed for halogen content

Solder Process Capability

Not reviewed for solder process capability

### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Also in the Series | [MEAS PT1](#)



Cable Actuated Position Sensors(1370)

## Documents

### Datasheets & Catalog Pages

PT1A

English