




Energy & Power > Arresters, Insulators & Insulation > Electrical Insulator Covers & Accessories > Bushing Guard



Product Availability: **Worldwide**

Installation Technology: **Cold Applied**

Voltage Class: **≤ 35 kV**

LV/MV Insulating Cover Product Type: **Arrester Cover**

Compatible Equipment: **Arrester**

[All Bushing Guard \(15\)](#)

## Features

### Product Type Features

Installation Technology	Cold Applied
LV/MV Insulating Cover Product Type	Arrester Cover

### Electrical Characteristics

Voltage Class	≤ 35 kV
---------------	---------

### Body Features

Primary Product Material	Crosslinked Polyolefin
Primary Product Color	Gray

### Dimensions

Insulator Outside Skirt Diameter Range	0 – 127 mm[0 – 5. in]
--	-----------------------

### Usage Conditions

Operating Temperature Range	0 – 105 °C
-----------------------------	------------

### Operation/Application

--	--



Power Component Application Type	Distribution
----------------------------------	--------------

Compatible Equipment	Arrester
----------------------	----------

### Industry Standards

Compatible With Agency/Standards Products	RUS
---	-----

### Product Availability

Product Availability	Worldwide
----------------------	-----------

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	<p>Current ECHA Candidate List: JUNE 2024 (241)</p> <p>Candidate List Declared Against: JAN 2024 (240)</p> <p>SVHC &gt; Threshold:</p> <p>UV-328 (1% in Component Part)</p> <p>UV-326 (.5% in Component Part)</p>
--	---

**Article Safe Usage Statements:**

Wash thoroughly after handling. Do not handle until all safety precautions have been read and understood. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not applicable for solder process capability
---------------------------	--

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # CL6659-000  
BCAC-G-CUTOUT-200(B3)



TE Part # ED6436-000  
BCAC-G-AR-4D-2(B24)



TE Part # ES4051-000  
BCAC+G-AR-5D-2(B24)




TE Part # ES4052-000  
BCAC+G-AR-4D-2(B24)



TE Part # ES4053-000  
BCAC+G-AR-3.75D-2(B24)

## Also in the Series | RAYCHEM BCAC



Electrical Insulator Covers & Accessories(49)

## Customers Also Bought



TE Part # CR8835-000  
BISG-24-01(B10)



TE Part # CP4754-000  
Voltage Conductor Cover MVCC (MV)



TE Part # B57744-000  
BCAC-P-IC-5D/6(B6)



TE Part # CP7898-000  
BCIC-G-DPIN-556-01(B6)



TE Part # EH8276-000  
CSTO-282G



TE Part # EN7339-000  
WLG-60(B1)



## Documents

### Product Drawings

[BCAC-G-AR-5D-2\(B24\)](#)

English

---

### Datasheets & Catalog Pages

[WILDLIFE & ASSET PROTECTION](#)

English

[BCAC BUSHING CONNECTION ANIMAL COVER](#)

English

[RAYCHEM SURGE ARRESTER CONNECTION COVER \(BCAC\)](#)

English