



AST | AST43LP

TE Internal #: 11192552-00

Industrial Pressure Transducer, Gauge, Non-Incendive, 4 – 20 mA

Output Signal Type, 2X, Min Proof Pressure Range, AST43LP

[View on TE.com >](#)

Sensors > Pressure Sensors > Pressure Transducers > Non-Incendive Low Pressure Transducer



Pressure Sensor Type: **Industrial Pressure Transducer**

Pressure: **.517 bar [ 7.5 psi ]**

Pressure Type: **Gauge**

Hazardous Area Approval: **Non-Incendive**

Supply Voltage Range: **10 – 28 V**

[All Non-Incendive Low Pressure Transducer \(18\)](#)

## Features

### Product Type Features

Pressure Sensor Type	Industrial Pressure Transducer
Pressure Type	Gauge

### Configuration Features

Electrical Connection	Conduit 10 ft
-----------------------	---------------

### Electrical Characteristics

Supply Voltage Range	10 – 28 V
----------------------	-----------

### Dimensions

Product Diameter	22.22 mm [.875 in]
Product Length	3075.9 mm [121.1 in]

### Usage Conditions

Pressure	.517 bar [7.5 psi]
Operating Temperature Range	-40 – 80 °C [-40 – 176 °F]

### Operation/Application

Output Signal Type	4 – 20 mA
Proof Pressure Range	2X, Min
Pressure Accuracy	±0.25% FSO



### Industry Standards

Compatible With Agency/Standards Products	UL
Hazardous Area Approval	Non-Incendive

### Other

Sensor Options	Increased Proof Pressure
Port Fitting	1/4 MNPT

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Yet Reviewed
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability


#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

### Compatible Parts



## Also in the Series | **AST43LP**



## Documents

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_11192552-00\\_A.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_11192552-00\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_11192552-00\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[AST43LP Pressure Transducer Datasheet](#)

English