

# AST4300A06000P4L1000 × OBSOLETE



[AST](#) | [AST4300](#)

TE Internal #: 11192623-00

TE Internal Description: 6000 PSI, 1/4MNPT, 4-20mA, Conduit, 2ft.

Non-Incendive Pressure Transducer

[View on TE.com >](#)

[Sensors](#) > [Pressure Sensors](#) > [Pressure Transducers](#) > [Non-Incendive Pressure Transducer](#)



Pressure Sensor Type: **Industrial Pressure Transducer**

Pressure Type: **Gauge**

Hazardous Area Approval: **Non-Incendive**

Output Signal Type: **4 – 20 mA**

Pressure: **414 bar [ 6000 psi ]**

[All Non-Incendive Pressure Transducer \(103\)](#)

## Features

### Product Type Features

Pressure Sensor Type	Industrial Pressure Transducer
----------------------	--------------------------------

Pressure Type	Gauge
---------------	-------

### Configuration Features

Electrical Connection	Conduit 2 ft
-----------------------	--------------

### Electrical Characteristics

Supply Voltage Range	10 – 28 V
----------------------	-----------

### Body Features

Port Material	316L
---------------	------

### Usage Conditions

Pressure	414 bar[6000 psi]
----------	-------------------

### Operation/Application

Output Signal Type	4 – 20 mA
--------------------	-----------

Proof Pressure Range	2X, Min
----------------------	---------

Pressure Accuracy	±0.25% FSO
-------------------	------------

### Industry Standards

Compatible With Agency/Standards Products	UL
---	----

Hazardous Area Approval

Non-Incendive

### Other

Sensor Options

No Option

Port Fitting

1/4 MNPT

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU

Not Yet Reviewed

EU ELV Directive 2000/53/EC

Out of Scope

China RoHS 2 Directive MIIT Order No 32, 2016

未针对中国 RoHS 符合性进行审核 Not reviewed for China RoHS compliance

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2025 (250)  
Not Yet Reviewed

Halogen Content

Not Yet Reviewed for halogen content

Solder Process Capability

Not reviewed for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Also in the Series | [AST4300](#)




Industrial Pressure Transducers(103)



Pressure Transducers(103)

## Customers Also Bought



## Documents

### CAD Files

#### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_11192623-00\\_A.2d\\_dxf.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_11192623-00\\_A.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_11192623-00\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[AST4300 Pressure Transducer Datasheet](#)

English