





MLF2012A2R2KT000

Applications		Commercial Grade
Feature		Multilayer
		Magnetic Shield
		Ferrite Core
Series	MLF Series / MLF2012 Type	
Status	Production	



Size	
Length(L)	2.00mm +/-0.20mm
Width(W)	1.25mm +/-0.20mm
Thickness(T)	0.85mm +/-0.20mm
Recommended Land Pattern (A)	0.80mm Nom.
Recommended Land Pattern (B)	1.00mm Nom.
Recommended Land Pattern (C)	1.20mm Nom.


Electrical Characteristics	
Inductance	2.2uH +/-10% at 10MHz
Rated Current	50mA
Self-Resonant Frequency [Min.]	80MHz
Self-Resonant Frequency [Typ.]	120MHz
Q [Min.]	45 at 10MHz
Q [Typ.]	60 at 10MHz
DC Resistance [Nom.]	220mΩ
DC Resistance [Max.]	500mΩ

Other	
Operating Temp. Range (Including Self-Temp. Rise)	-55 to 125degC
Soldering Method	Reflow, Iron Soldering
AEC Q200	No
Packing	Punched (Paper)Taping [180mm Reel]
Package Quantity	4000Pcs Min.
Weight	0.01g


•This PDF document was created based on the data listed on the TDK Corporation website.
 •All specifications are subject to change without notice.

MLF2012A2R2KT000


Characteristic Graphs (This is reference data, and does not guarantee the product's characteristics.)




MLF2012A2R2KT000



MLF2012A2R2KT000



MLF2012A2R2KT000






MLF2012A2R2KT000

- This PDF document was created based on the data listed on the TDK Corporation website.
- All specifications are subject to change without notice.

MLF2012A2R2KT000

Characteristic Graphs (This is reference data, and does not guarantee the product's characteristics.)



•This PDF document was created based on the data listed on the TDK Corporation website.
•All specifications are subject to change without notice.