

MLF2012D68NMT000

Applications	 Commercial Grade
Feature	 Multilayer
	 Magnetic Shield
	 Ferrite Core
Series	MLF Series / MLF2012 Type
Status	Production



Size	
Length(L)	2.00mm +/-0.20mm
Width(W)	1.25mm +/-0.20mm
Thickness(T)	0.85mm +/-0.20mm
Recommended Land Pattern (A)	0.80mm Nom.
Recommended Land Pattern (B)	1.00mm Nom.
Recommended Land Pattern (C)	1.20mm Nom.


Electrical Characteristics	
Inductance	68nH +/-20% at 50MHz
Rated Current	300mA
Self-Resonant Frequency [Min.]	500MHz
Self-Resonant Frequency [Typ.]	600MHz
Q [Min.]	15 at 50MHz
Q [Typ.]	25 at 50MHz
DC Resistance [Nom.]	80mΩ
DC Resistance [Max.]	150mΩ

Other	
Operating Temp. Range (Including Self-Temp. Rise)	-55 to 125degC
Soldering Method	Reflow, Iron Soldering
AEC Q200	No
Packing	Punched (Paper)Taping [180mm Reel]
Package Quantity	4000Pcs Min.
Weight	0.01g


•This PDF document was created based on the data listed on the TDK Corporation website.
 •All specifications are subject to change without notice.

MLF2012D68NMT000


Characteristic Graphs (This is reference data, and does not guarantee the product's characteristics.)




MLF2012D68NMT000



MLF2012D68NMT000



MLF2012D68NMT000






MLF2012D68NMT000

- This PDF document was created based on the data listed on the TDK Corporation website.
- All specifications are subject to change without notice.

MLF2012D68NMT000

Characteristic Graphs (This is reference data, and does not guarantee the product's characteristics.)



•This PDF document was created based on the data listed on the TDK Corporation website.
•All specifications are subject to change without notice.