

XUYFVPSD201

glass fibre optic for sensor - diffuse - straight -
standard - 2m - Sn80mm

Main

| | |
|-------------------------------|---|
| Range of product | OsiSense XU |
| Sensor name | XUY |
| Sensor design | Fiber design |
| Sheath type | Standard |
| [Sn] nominal sensing distance | 80 mm XUYAFV |
| End fitting type | Straight with nickel plated brass, M4 x 0.7 |

Complementary

| | |
|------------------------|--------------------------|
| Electronic sensor type | Photo-electric sensor |
| Optic fiber material | 50 µ glass |
| Sheath material | PVC + thermo polyolefine |
| Detection system | Diffuse |
| Optic fiber length | 2 m |
| Minimum bending radius | 10 mm |
| Head mounting | M4 x 0.7 |

Environment

| | |
|---------------------------------------|-------------|
| Ambient air temperature for operation | -25...60 °C |
|---------------------------------------|-------------|

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.