


4 and 5-Wire M12 eurofast® Receptacles, Front Mount, Leads and Solder Cups

- Male Receptacles
- NEMA 1, 3, 4, 6P
- IEC IP 68 Protection



Drawing Number	Part Number	Lead Specs.	Application	Pinout
<p><b>13</b></p> <p>FS .. /PG13.5</p>	FS 4.4-*/PG13.5	UL, CSA Nickel Plated Brass 4x22 AWG 105°C 250 V 4 A	Mates with 4-pin cordsets, PG 13.5 Threads	<ol style="list-style-type: none"> <li>1. BN</li> <li>2. WH</li> <li>3. BU</li> <li>4. BK</li> </ol>
	FS 4.5-*/PG13.5	UL, CSA Nickel Plated Brass 5x22 AWG 105°C 250 V 4 A	Mates with 5-pin cordsets, PG 13.5 Threads	<ol style="list-style-type: none"> <li>1. BN</li> <li>2. WH</li> <li>3. BU</li> <li>4. BK</li> <li>5. CY</li> </ol>
<p><b>14</b></p> <p>FS .. /18.25</p>	FS 4.4/18.25	105°C Solder Cup 300 V 4 A	Mates with 4-pin cordsets, 1/4 inch 18NPT Threads	N/A 
	FS 4.4	105°C Solder Cup 250 V 4 A	Mates with 4-pin cordsets, PG 9 Threads	
<p><b>15</b></p> <p>FS ..</p>	FS 4.5	105°C Solder Cup 250 V 4 A	Mates with 5-pin cordsets, PG 9 Threads	N/A 
	FS 4.4/14.5	105°C Solder Cup 250 V 4 A	Mates with 4-pin cordsets, 1/2-14NPSM Threads	N/A 
<p><b>16</b></p> <p>FS .. /14.5</p>	FS 4.5/14.5	105°C Solder Cup 250 V 4 A	Mates with 5-pin cordsets, 1/2-14NPSM Threads	N/A 

See page D114 for dimensional drawings.

\* Length in meters. Standard lead length is 0.5 Meters. Consult factory for other lengths.  
Standard housing material is nickel plated brass "FS."; "FSV.." indicates 316 stainless steel.  
To specify PVC jacketed cable, add "/S717" to the end of the part number.