

## 16-Port 10/100/1000 Mbps 1U Rack-Mount/Desktop Gigabit Ethernet Unmanaged Switch, Metal Housing

MODEL NUMBER: NG16



Energy-efficient unmanaged switch sets up in seconds with no configuration required. Provides a Gigabit network connection for multiple devices. Ideal for home or small offices, workgroups and creative production environments.

### Description

The NG16 16-Port 10/100/1000 Mbps 1U Rack-Mount/Desktop Gigabit Ethernet Unmanaged Switch adds 10/100/1000 Mbps Ethernet capacity to your home office, small office, workgroup or creative production environment. Share large bandwidth-intensive files, such as CAD drawings and videos, at Gigabit speeds, improving efficiency and cutting costly downtime.

This rack-mount/desktop switch features 16 twisted-pair RJ45 Gigabit Ethernet ports that support auto-negotiable 10/100/1000 Mbps and auto MDI/MDIX cross-over detection functions for convenient plug-and-play capability. No configuration is required, so you can have your Gigabit network up and running immediately. Easy-to-read LEDs indicate connection and activity status for each port. IEEE 802.3x flow control allows smooth transmission of large files.

The NG16 supports IEEE 802.3az Energy Efficient Ethernet standards by putting unused ports into a low-power state without interrupting network connections. It consumes very little input power—just seven watts max. The detachable five-foot input cord with NEMA 5-15P plug connects to a protected UPS, generator or mains input AC source. The heavy-duty metal housing is designed for desktop installation or mounting into 1U of an EIA-standard 19-inch rack with the included brackets.

### Features

#### Unmanaged Network Switch for Home/Small Offices or Workgroups

- 16 twisted-pair RJ45 Gigabit Ethernet ports

### Highlights

- 16 auto-negotiable 10/100/1000 Mbps RJ45 ports
- Supports auto MDI/MDIX cross-over function
- Consumes very little input power—just 7W max
- 2 Gbps switching capacity per port with full duplex
- Plug-and-play with no configuration required

### Package Includes

- NG16 16-Port 10/100/1000 Mbps 1U Rack-Mount/Desktop Gigabit Ethernet Unmanaged Switch
- Detachable AC power cord with NEMA 5-15P plug, 5 ft.
- (2) Mounting brackets
- (8) Screws
- (4) Rubber feet
- Owner's manual



- Auto-negotiable 10/100/1000 Mbps
- Automatic MDI/MDIX cross-over detection
- 32 Gbps switching capacity (2 Gbps per port with full duplex)
- Easy-to-read LEDs indicate connection and activity status for each port
- Supports 9k jumbo frames
- Supports MAC address auto-learning and auto-aging
- Supports 802.3x flow control (full duplex) and back pressure (half duplex)

#### **Compliant with IEEE 802.3az Energy Efficient Ethernet Standards**

- Automatically shifts unused ports to low-power state without interrupting network connection
- Consumes very little input power—just 7W max
- Also meets IEEE 802.3ab, 802.3i, 802.3u and 802.3 standards

#### **Heavy-Duty Metal Housing**

- Fanless design for silent operation
- Detachable 5 ft. AC power cord with NEMA 5-15P plug
- Plug-and-play—no configuration necessary

#### **Versatile Installation Options**

- Includes rubber feet for secure placement on flat desktop surface
- Mounts in 1U of EIA-standard 19 in. rack with included brackets
- Grounding lug included

## Specifications

OVERVIEW	
UPC Code	037332194725
Product Type	Unmanaged Switch
INPUT	
Electrical Consumption (Max)	7W
Nominal Input Voltage Description	Accepts 100-240V AC nominal input
Plug Type	Includes NEMA 5-15P input plug
Voltage Compatibility (VAC)	100-240
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	5
Input Cord Length (m)	1.52
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Power LED (Green for Power On); One LED per RJ45 port (Green indicates 10/100Mbps link; Amber indicates 1000Mbps link; LEDs flash to indicate port activity)



<b>PHYSICAL</b>	
Primary Form Factor	Desktop; Rackmount
Color	Black
Form Factors Supported	Desktop, Rackmount
Shipping Dimensions (hwd / cm)	7.62 x 24.64 x 43.69
Shipping Dimensions (hwd / in.)	3.00 x 9.70 x 17.20
Shipping Weight (kg)	2.22
Shipping Weight (lbs.)	4.90
Unit Dimensions (hwd / cm)	4.42 x 27.99 x 18.01
Unit Dimensions (hwd / in.)	1.74 x 11.02 x 7.09
Unit Weight (kg)	1.45
Unit Weight (lbs.)	3.2
Rack Units	1
<b>ENVIRONMENTAL</b>	
Storage Temperature Range	-40 to 158F (-40 to 70C)
Relative Humidity	10 to 90% (non-condensing)
Operating Temperature	32 to 104F (0 to 40C)
Power Consumption (Watts)	7
Fans (Type/Quantity)	Fanless
<b>COMMUNICATIONS</b>	
Network Compatibility	Gigabit Ethernet (10/100/1000)
Network Compatibility Details	Auto-negotiable
Switching Capacity	32 Gbps
Switching Capacity Details	2 Gbps per port with full duplex
<b>CONNECTIONS</b>	
RJ45 Ports	16
RJ45 Ports Detail	16x 10/100/1000BASE-T
SFP Uplink Ports	0
PoE Supported Ports	0
Network Switch Ports	(16) 10/100/1000 (RJ45)
<b>FEATURES &amp; SPECIFICATIONS</b>	
Jumbo Frames	9000



Console Port	No
MAC Auto Learning	Yes
RMON	No
SNMP	No
Storm Control	No
DHCP Snooping	No
Auto MDI/MDIX Crossover Detection	Yes
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	Compliant Standards: IEEE 802.3ab (1000BASE-T GIGABIT ETHERNET), IEEE 802.3i (10BASE-T ETHERNET), IEEE 802.3u (100BASE-T ETHERNET), IEEE 802.3x (FULL DUPLEX/FLOW CONTROL), IEEE 802.3 (NWAY AUTO-NEGOTIATION), 802.3az (ENERGY EFFICIENT ETHERNET)
Approvals	Tested to North American safety and EMI standards UL60950-1: 2007 (2ND ED) +A1+A2 R14; CAN/CSA C22.2 NO. 60950-1-07, 2ND EDITION, 2014-10; FCC Class B; RoHS Compliant
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>