

## Specification Sheet

Part Number: 111-01196



PA66HIRHSUV material is formulated to withstand extreme climate conditions and vibration.

Inside serrations enhance strong grip on cables and wire bundles.

Head design provides high tensile strength with low insertion force.

Bent tail ensures a quick and simple installation.

Article Number 111-01196

Type T250M

Color Black (BK)

Quantity Per bag

Product Description These cable ties are manufactured from a specially formulated impact-resistant, heat and UV stabilized PA66 material, delivering increased flexibility while also enduring moisture fluctuations. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description Heavy Duty Cable Tie, 22" Long, UL Rated, 250lb Tensile Strength, PA66HIRHSUV, Black, 25/pkg

Global Part Name T250M-PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial) 250

Minimum Tensile Strength (Metric) 1115

Length L (Imperial) 22.3

Length L (Metric) 565.3

Identification Plate Position none

Releasable Closure No

Tie Closure plastic pawl

Variant Inside Serrated

Width W (Imperial) 0.49

Width W (Metric) 12.4

Bundle Diameter Min (Imperial) 0.47

Bundle Diameter Min (Metric) 12.0

Bundle Diameter Max (Imperial) 5.91

Bundle Diameter Max (Metric) 150.0

Thickness T (Imperial) 0.07

Thickness T (Metric)	1.9
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	25
Package Quantity (Metric)	25
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)