





MARKETING SALES DRAWING

DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []

Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.



MOUNTING HARDWARE



NOTES:

1. OPERATING TEMPERATURE RANGE: -55°C TO +125°C.
2. SILVER PLATED CASE, LEAD AND MOUNTING HARDWARE.
3. MAX. RECOMMENDED MOUNTING TORQUE : 2.0 lb. - in.
4. MAX. RECOMMENDED SOLDERING TEMPERATURE : 260°C.
SEE INSTALLATION RECOMMENDATIONS.
5. NUT AND LOCKWASHER INCLUDED.
6. TUSONIX TRADEMARK AND PART VARIATION NUMBER
STAMPED ON HEX FLATS.

27,000	GMV	70	50	10	10	28	42	65	65
CAP.(pf)	TOLERANCE	85 °C	125 °C	DC	1 MHz	10 MHz	100 MHz	1 GHz	10 GHz
		DC WORKING VOLTAGE		CURRENT (AMPS)	MINIMUM NO LOAD INSERTION LOSS (dB) AT 25°C PER MIL-STD-220				

REVISION RECORD					--TOLERANCES-- Unless Otherwise Specified		Title MINIATURE BUSHING STYLE EMI FILTER		
	Original Release					DECIMAL ± NOTED			
	WAS SK 8025-000					ANGLES ± NOTED	Drawn	S.M. 10-11-01	Scale 8 X
	L.E. 10-17-01						Approved	B.Mc. 10-11-01	
	20011015-4-04					TUSONIX TUCSON, ARIZONA	A	4403-060	