

Specification Sheet

Part Number: 156-00882

Friction tab inside the fir tree allows the tie to sit in mount without falling out prior to installation.

Fir tree provides low insertion effort yet demonstrates high extraction resistance.

Disc feature prevents rattling in high-vibration applications and protects against debris ingress.



Article Number	156-00882
Type	T50RFT5.5SD
Color	Black (BK)
Quantity Per	pack
Product Description	HellermannTyton's fir tree mounts provide a secure grip in a mounting hole. The mount can slide along the cable tie to adjust orientation as needed. Fir tree mounts are designed to provide a low insertion force and high extraction force. This mount is sold as an assembly with the cable tie.
Short Description	2-Piece Cable Tie with Fir Tree Mount, 8.0"L, 0.20 - 0.22" Mounting Hole Diameter, PA66HS, Black, 500/pkg
Global Part Name	T50RFT5.5SD-PA66HS/PA66HIRHS-BK

Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	8.0
Length L (Metric)	203.2
Fixation Method	Fir tree for round holes
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Width W (Imperial)	0.18
Width W (Metric)	4.6
Bundle Diameter Min (Imperial)	0.2
Bundle Diameter Min (Metric)	5.0
Bundle Diameter Max (Imperial)	1.77
Bundle Diameter Max (Metric)	45.0
Thickness T (Imperial)	0.05
Thickness T (Metric)	1.2

Height H (Imperial)	0.05
Panel Thickness Min (Imperial)	0.03
Panel Thickness Max (Imperial)	0.18
Panel Thickness Min (Metric)	0.7
Panel Thickness Max (Metric)	4.5
Mounting Hole Diameter D (Imperial)	0.2 - 0.22 "
Mounting Hole Diameter D (Metric)	5.0 - 5.7 mm
Mounting Hole Diameter D Min (Imperial)	0.2
Mounting Hole Diameter D Max (Imperial)	0.22
Mounting Hole Diameter D Max (Metric)	5.7
Disc Diameter (Metric)	16.0
Disc Diameter (Imperial)	0.63
Material	Polyamide 6.6 heat stabilized (PA66HS) Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Foot Part Material	PA66HIRHS
Material Shortcut	PA66HS PA66HIRHS

Material Cable Tie	Polyamide 6.6 heat stabilized (PA66HS)
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)