

Specification Sheet


Part Number: IT50RT9K2

Identification plate feature allows bundles to be easily marked and identified.

Wire and cable harnesses can be secured and identified using just one product, which saves time.

Plates can be marked manually with a permanent marker or with a pre-printed adhesive label.

Complies with MS3368-4-9D, Class 1 and SAE-AS33681.



MilSpec Identification Tie, 8" Long, MS3368, 50lb Tensile Strength, PA66, Natural, 50/pkg

Article Number 111-85119

Type IT50RT

Color Natural (NA)

Quantity Per pack

Product Description Identification Cable Ties feature an identification plate that allows wire and cable bundles to be easily marked and identified. These ties enable wire and cables to be secured and identified using just one product, saving installation time. The plates can be marked using a permanent marker or with a HellermannTyton adhesive label. Specially manufactured to comply with Military Specification MS3368-4-9D, Class 1 and SAE-AS33681.

Short Description	MilSpec Identification Tie, 8" Long, MS3368, 50lb Tensile Strength, PA66, Natural, 50/pkg
Global Part Name	IT50RT-PA66-NA
Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	8.0
Length L (Metric)	203.2
Fixation Method	None
Identification Plate Position	attached to bundle
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	1.8
Width W (Metric)	46.0
Bundle Diameter Min (Imperial)	0.39
Bundle Diameter Min (Metric)	10.0
Bundle Diameter Max (Imperial)	1.73

Bundle Diameter Max (Metric)	44.0
Thickness T (Imperial)	0.05
Thickness T (Metric)	1.2
Height H (Imperial)	1.04
Height H (Metric)	26.3
Outside Diameter Max (Imperial)	1.73
Outside Diameter Min (Metric)	10.00
Outside Diameter Min (Imperial)	0.393
Outside Diameter Max (Metric)	44.00
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
US MIL SPEC	SAE-AS33681 MS3368-4-9D, Class 1
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant (Yes/No)	No

Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL ANSI/UL 746B UL ANSI/UL 62275 UL ANSI/UL 1565 CAGE Code 53421
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	50
Package Quantity (Metric)	50
Customs Number	3926909988
Weight (Metric)	2.5

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)