

Specification Sheet

Part Number: CTM010M4



KR/CTM series are designed to provide stability to wire bundles.

These mounts can accommodate miniature, intermediate, or standard cross-section cable ties.

Each mount is secured with a single screw.

Cable Tie Anchor Mount, 0.58 x .37", 0.15" Hole Dia, 0.2" Max Tie Width, PA66, White, 1000/pkg

Article Number	151-30305
----------------	-----------

Type	CTM0
------	------

Color	White (WH)
-------	------------

Quantity Per	pack
--------------	------

Product Description	Designed specifically for holding heavier cable bundles these mounting bases can be used in many industries from agriculture to truck manufacture. They offer a very secure fixing and can be used with a wide variety of heavy duty cable ties up to 8.3 mm width.
---------------------	---

Short Description	Cable Tie Anchor Mount, 0.58 x .37", 0.15" Hole Dia, 0.2" Max Tie Width, PA66, White, 1000/pkg
-------------------	--

Global Part Name	CTM0-PA66-WH
------------------	--------------

Length L (Imperial)	0.58
Length L (Metric)	14.7
Fixation Method	Screw Mount
Width W (Imperial)	0.37
Width W (Metric)	9.4
Cable Ties	T18 - T50
Height H (Imperial)	0.27
Height H (Metric)	6.9
Cable Tie Width Max (Imperial)	0.2
Cable Tie Width Max (Metric)	5.0
Mounting Hole Diameter D (Imperial)	0.15 "
Mounting Hole Diameter D (Metric)	3.8 mm
Mounting Hole Diameter D Max (Metric)	3.8
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66

Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL-ZODZ2.E64139
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)