



Distributed by:

JAMECO[®]
ELECTRONICS



www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

CNX D F 2 6 XX



Recommended LEDs which meet critical dimension.
 Kingbright, Stanley, Liteon, & Sun LED
 when using CNX connectors.



Customer Name: _____

Address: _____

Customer Contact: _____

Phone: _____ Fax: _____

Customer' approval: _____

Date of approval : _____

CABLE ASSEMBLY BILL OF MATERIALS

ITEM	P/N	DESCRIPTION	COLOR	LENGTHS
A	450230	5MM CONNECTOR		STANDARD
B	450303	3 POSITION LOCKING HEADER CONNECTOR		4 INCH 6 INCH 8 INCH 10 INCH 12 INCH 18 INCH 24 INCH OPTIONAL LENGTHS AVAILABLE
1	WIRE	22 AWG 1007 / 1569	WHITE	
2	WIRE	22 AWG 1007 / 1569	BLACK	
3	WIRE	22 AWG 1007 / 1569	RED	

U.S. / FOREIGN PAT. ISSUED & PEND.

NOTES:

- Material: U.L. Rating - "Thermoplastic material used on a secondary circuit"
- Wire: 22 awg (105° C) color Red / Black / White
- Panel Mounting: CML 325 lense - panel hole size .281 " Retaining ring may be require for panel thickness from .030" to .170". Panels from .190" to .240 ring not required
PCB Mounting: VCC Pin Header, positive locking series or equal

REVISIONS			
NO	DESCRIPTION	DATE	BY
1			
2			
3			
4			
5			

VCC P/N: CNX D F 2 6 XX

VCC VISUAL COMMUNICATIONS COMPANY, INC.
 7920-F Arjons Drive San Diego, California 92126 U.S.A.
 Phone (858) 549-6900 Fax (858) 549-3520 e-mail vccsales@vccite.com

TOLERANCES	SCALE	N/A	DATE	03/04/99	DRAWING NO.
DECIMAL	±.500	DIAMETER	DRAWN BY	JMS	
ANGLE		RADII	CHK'D		