

Item no.: 282-904
Product description: 2-CONDUCTOR THROUGH TERMINAL BLOCK; CENTRE MARKING; SUITABLE FOR EX I APPLICATIONS; for DIN 35 rail; FRONT-ENTRY; CAGE CLAMP®CONNECTION



Packing unit 50 pieces

Product group	1 (Rail Mounted Terminal Blocks)
Cross section from [mm ²]	0,2 mm ²
Cross section to [mm ²]	6 mm ²
Cross section from [AWG]	24 AWG
Cross section to [AWG]	10 AWG
Connection method	CAGE CLAMP®CONNECTION
Measured voltage EN	800 V
Measured shock voltage	8 kV
Pollution degree	3
Current intensity EN	41 A
Weight	16,046 g
Color	blue
Wiring type	Front-entry
No. of connection Points	2
No. of potentials	1
Height	32,5 mm
Height	1,28 in
Width	8 mm
Width	0,315 in
Depth	74,5 mm
Depth	2,93 in
Strip length from	12 mm
Strip length to	13 mm
Strip length	0,49 in



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
282-904	ABS	05-HG476175/1-PDA	800	32	6,0
282-904	BV	07436/Co	800	32	6,0
282-904	CCA	NL5448	800	30	6
282-904	CSA	154112-1505033	600	40	24-10
282-904	DNV	E7570	800	41	6,0
282-904	GL	17295-00HH	800	41	6
282-904	KEMA	2036066.01	800		6
282-904	LR	91/20112(E5)	800	32	6,0
282-904	PRS	TE/1718/880590/08	800	30	6
282-904	RMR	11130002	800	32	6,0
282-904	UR	E45172	600	30	24-10

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected