

| : 726-672


Common potential matrix patchboard; Marking 1-24; with 2 input modules incl. end plate; Color of modules: green-yellow; Numbering of modules arranged vertically; for 19" racks; Slimline version; 16,00 mm²; dark gray



<https://www.wago.com/726-672>



■ dark gray



Connection data

Connection 1

Connection type 1	Page 1
Connection technology	Push-in CAGE CLAMP®
Number of connection points	2
Actuation type	Operating tool
Connectable conductor materials	Copper
Solid conductor	0.2 ... 16 mm ² / 24 ... 6 AWG
Fine-stranded conductor	0.2 ... 16 mm ² / 24 ... 6 AWG
Strip length	16 ... 17 mm / 0.63 ... 0.67 inches
Wiring direction	Front-entry wiring

Connection 2

Connection type 2	Page 2
Connection technology 2	CAGE CLAMP®
Number of connection points 2	2
Solid conductor 2	0.08 ... 2.5 mm ² / 28 ... 14 AWG
Fine-stranded conductor 2	0.08 ... 2.5 mm ² / 28 ... 14 AWG
Strip length 2	8 ... 10 mm / 0.31 ... 0.39 inches

Physical data

Width	34.6 mm / 1.362 inches
Height	132 mm / 5.197 inches
Depth	80.7 mm / 3.177 inches

Mechanical Data

Marking	1 ... 24
Design	slimline

Material Data

Note (material data)

[Information on material specifications can be found here](#)

Color dark gray

Module color green-yellow

Material group I

Insulation material Polyamide (PA66)

Flammability class per UL94 V0

Fire load 1.187 MJ

Weight 264.5 g

Commercial data

eCl@ss 10.0 27-24-26-08

eCl@ss 9.0 27-24-26-08

ETIM 8.0 EC001604

ETIM 7.0 EC001604

PU (SPU) 10 (1) pcs

Packaging type Box

Country of origin DE

GTIN 4055143623520

Customs tariff number 85369010000

Approvals / Certificates

General approvals



CCA DEKRA Certification B.V.	EN 60998	NTR NL-7623
---------------------------------	----------	-------------

CSA CSA Group	C22.2 No. 158	1101143
------------------	---------------	---------

KEMA/KEUR DEKRA Certification B.V.	EN 60998	71-100850
---------------------------------------	----------	-----------

UL UL International Germany GmbH	UL 1059	E45172
--	---------	--------

Downloads


Environmental Product Compliance



Compliance Search

Environmental Product
Compliance 726-672





Documentation

Additional Information		
Technical Section	pdf 2142.18 KB	

Bid Text			
726-672	19.02.2019	xml 3.42 KB	
726-672	21.02.2019	docx 14.64 KB	

CAD/CAE-Data

CAE data		
EPLAN Data Portal 726-672		
WSCAD Universe 726-672		

1 Compatible Products

1.1 Optional Accessories

1.1.1 Jumper

1.1.1.1 Jumper



[: 709-107](#)
Wire commoning chain; 0.5 mm²; insulated; gray

1.1.2 Marking

1.1.2.1 Marker



[: 793-5501/000-006](#)
WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type; blue



[: 793-5501/000-014](#)
WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type; brown



[: 793-5501/000-007](#)
WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type; gray



[: 793-5501/000-023](#)
WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type; green



[: 793-5501/000-017](#)
WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type; light green



[: 793-5501/000-012](#)
WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type; orange



[: 793-5501/000-005](#)
WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type; red



[: 793-5501/000-024](#)
WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type; violet



[: 793-5501](#)
WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type; white



[: 793-5501/000-002](#)
WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type; yellow

[: 2009-115](#)
WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; white

1.1.2.2 Marker carrier



: [726-902](#)

Adaptor; dark gray

1.1.2.3 Marking strip



: [2009-110](#)

Marking strips; for Smart Printer; on reel; not stretchable; plain; snap-on type; white

1.1.3 Terminal blocks

1.1.3.1 Ground terminal block



: [2016-7607](#)

2-conductor ground terminal block; 16 mm²; side and center marking; for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®; 16,00 mm²; green-yellow

1.1.3.2 Supply module



: [2016-7607](#)

2-conductor ground terminal block; 16 mm²; side and center marking; for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®; 16,00 mm²; green-yellow

Installation Notes

Conductor termination



CAGE CLAMP® connection
Inserting a conductor via 210-719 Operating Tool (2.5 x 0.4 mm blade).

Testing



Testing with a 2.3 mm Ø test plug (210-137).




Snapping on an additional module with contact to mounting frame.



Assembling a matrix patchboard with additional module – direct connection to the mounting frame.

Marking



Factory-marked modules (Side 1: 1, 2, 3, 4 ...)



Individual group marking via WMB Multi Marking System