



WAGO-I/O-CHECK is an easy-to-use Windows application for operating and displaying a WAGO I/O System 750's node without connecting to a fieldbus system.

The software reads the configuration from the node and displays it graphically on the screen. This graphic can be printed together with a configuration list as documentation.

With WAGO-I/O-CHECK, it is possible to display and specify the process data of the I/O modules. The field wiring, including all sensors and actuators, can thus be checked before startup.

For some types of interface, Pt100 and thermocouple modules, application-specific settings can be made, such as the baud rate or sensor types.

The coupler must be connected to a free serial or USB port of the PC using the communication cable supplied in the set with the system to enable communication between WAGO-I/O-CHECK and the node.

System requirements

Supported operating systems	Windows 7 Windows 10
Processor	1 GHz or higher, with 32 bits (x86) or 64 bits (x64)
Memory	Min. 1 GB RAM 2 GB RAM or more (recommended)
Hard disk space	min. 150 MB
Graphics resolution	1024 x 786 (min.), 1280 x 1024 or higher (recommended)

Delivery

Delivery type	Installation file (CD-ROM)
Scope of delivery	CD-ROM with software and serial communication cable (750-920)

Commercial data

eCl@ss 10.0	27-24-25-90
eCl@ss 9.0	27-24-25-90
ETIM 8.0	EC001435
ETIM 7.0	EC001435
PU (SPU)	1 pcs
Packaging type	Box
Country of origin	DE
GTIN	4045454394899
Customs tariff number	85234920009

Environmental Product Compliance

RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

Downloads

Environmental Product Compliance

Compliance Search			
Environmental Product Compliance 759-302			↓

Documentation

Manual			
Product Manual WAGO-I/O-CHECK Commissioning Tool for WAGO-I/O-SYSTEM 750	V 1.2.0	pdf 1158.70 KB	↓

System Description			
Software – General Product Information		pdf 368.80 KB	↓

Bid Text			
759-302	19.02.2019	xml 4.80 KB	↓
759-302	10.01.2019	docx 16.26 KB	↓

Subject to changes. Please also observe the further product documentation!

Current addresses can be found at: www.wago.com