


Delivered without miniature WSB markers

The I/O module generates 5V, 8V, 10V, 12V and 15V DC output voltages from the 24VDC input voltage.
 The output voltage is selected by a DIP switch located on the side of the module.
 The output voltage can be tapped at the CAGE CLAMP® connections.
 The adjoining modules are also supplied with this voltage level via the power jumper contacts.
 Status LEDs indicate the module's operating state.
 The input voltage and the output voltage are not electrically isolated.

Description	Item No.	Pack. Unit
Supply Module DC 24V / 5-15V	750-623	1
Accessories		
Miniature WSB Quick marking system		
 plain	248-501	5
with marking	see pages 352 ... 353	
Approvals		
Also see "Approvals Overview" in Section 1		
Conformity marking	CE	
Shipbuilding	GL	
UL 508		

Technical Data	
Power supply	24 V DC (-15 % ... +20 %)
Output voltage	5 V, 8 V, 10 V, 12 V, 15 V DC
Output current	0.5 A (1 A at 5 V)
Wire connection	CAGE CLAMP®
Cross sections	0.08 mm² ... 2.5 mm² / AWG 28 ... 14
Stripped lengths	8 ... 9 mm / 0.33 in
Width	12 mm
Weight	37.016 g
EMC: CE - immunity to interference	acc. to EN 61000-6-2 (2005)
EMC: CE - emission of interference	acc. to EN 61000-6-3 (2007)