






Similar to illustration



- Short description:**
- PUR, halogen-free
 - Suitable for drag chains
 - High resistance to microbes, hydrolysis, oil, chemicals and UV radiation
 - High chemical resistance
 - Cable used: UL listed

Technical data			
General		Suitable for drag chains	
Operating voltage	250 VAC/DC	Bending radius	10 x cable diameter (min.)
Operating current	4 A	Bending cycles	2 million
Rated surge voltage	2.5 kV	Acceleration (min.)	5 m/s ²
Contact resistance	10 mΩ	Travel speed (max.)	3.33 m/s
Conductor resistance	≤ 60 Ω/km	Travel path (horizontal) max.	5 m
Pollution degree (5)	3 per VDE 0110	Travel path (vertical) max.	2 m
Protection type	IP67	Torsional capacity	180 °/m
Ambient (operating) temperature (static)	-50 ... +90 °C		
Ambient (operating) temperature (dynamic)	-25 ... +90 °C		



Cable	
Cable length	1 m
Type code	LiF9YH-11YH or LiF9YC11YFHF
Conductor configuration	Bare copper wire, fine-stranded (42 x 0.1 mm)
Conductor insulation	PP9Y (halogen-free)
Sheath material	Polyurethane (PUR), halogen-free per DIN VDE 0472 Part 815, flame resistant per IEC 332-2, self-extinguishing
Sheathed cable color	black
Sheathed cable diameter	4.5 ... 4.9 mm

Connector	
Connection type	M12 Socket; M12 Socket - M12 plug
Cable connection direction to mating direction	90 °
Cable connection direction to mating direction (2)	0 °
Connector interface coding (cable/adaptor) 1 1	A-coded
Connector interface coding (cable/adaptor) 1 2	A-coded
Connector interface coding (cable/adaptor) 2 1	A-coded
Housing material	Polyurethane (PUR)
Contact material	CuSn
Tightening torque	1 Nm

Commercial data	
eCl@ss 10.0	27-06-03-11
eCl@ss 9.0	27-06-03-11
ETIM 8.0	EC001855
ETIM 7.0	EC001855
PU (SPU)	10 (1) pcs
Packaging type	Box
Country of origin	DE
GTIN	4044918994880
Customs tariff number	85444290900

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance
756-5517/040-010

↓

Documentation

System Description

IP67 Cables and Plug-gable Connectors

pdf
157.80 KB

↓

Additional Information

EU-Declaration of Con-formity

pdf
90.86 KB

↓

Bid Text			
756-5517/040-010	19.02.2019	xml 3.14 KB	↓
756-5517/040-010	20.09.2017	doc 26.50 KB	↓

CAD/CAE-Data



CAE data	
WSCAD Universe 756-5517/040-010	