

**CableLine**  
**CLI C 1-3 SW/WS 0 MP**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm<sup>2</sup> to max. 70 mm<sup>2</sup>. The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

**General ordering data**

Type	CLI C 1-3 SW/WS 0 MP
Order No.	<a href="#">0252611503</a>
Version	CableLine, Conductor and cable markers, 2.5 - 5 mm, 3 x 4.2 mm, black
GTIN (EAN)	4032248005314
Qty.	200 pc(s).

Creation date August 16, 2020 11:14:25 PM CEST

Catalogue status 24.07.2020 / We reserve the right to make technical changes.

**CableLine**  
**CLI C 1-3 SW/WS 0 MP**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**
**Dimensions and weights**

Width	4.2 mm	Width (inches)	0.165 inch
Height	3 mm	Height (inches)	0.118 inch
Depth	5 mm	Depth (inches)	0.197 inch
Net weight	0.05 g		

**General data**

Colour	black	Colour of printing	white
Halogen	Yes	Insulation cross-section, max.	5 mm
Material	PVC, soft, without Cadmium	Material colour according to resistance code	0
Operating temperature range	-30...80 °C	Orientation of print	horizontal
Printed characters	Numbers	Printing	0
Printing method	hot-embossing	Recommended industries	Process, Machinery
Type of printing	Standard	UL 94 flammability rating	V-0
Version	MultiPack	Width	4.2 mm

**Conductor and cable markers**

Conductor O.D.	2.5 - 5 mm	Conductor O.D., max.	5 mm
Conductor O.D., min.	2.5 mm	Conductor cross-section, max.	4 mm <sup>2</sup>
Conductor cross-section, min.	1.5 mm <sup>2</sup>	Halogen	Yes

**Classifications**

ETIM 6.0	EC001530	ETIM 7.0	EC001530
eClass 9.0	27-40-04-01	eClass 9.1	27-40-04-01
eClass 10.0	27-40-04-01	UNSPSC	44-12-17-08

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Engineering Data	<a href="#">EPLAN, WSCAD</a>
Product Change Notification	<a href="#">PCN CableLine_DE</a> <a href="#">PCN CableLine_EN</a>