

FPL 4G2.5/PD/F/3+3

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Take advantage of our pre-assembled FieldPower® connectors with HQ connectors acc. to IEC 23570 (DESINA) for connecting decentralised motor controller devices quickly and conveniently.

General ordering data

| | |
|------------|--|
| Version | FieldPower®, Cable, Number of wires: 4, Ölflex Classic 110 4G2.5 or similar, Cross-section: 2.5 mm ² , 3 m, 3 m |
| Order No. | 1059170000 |
| Type | FPL 4G2.5/PD/F/3+3 |
| GTIN (EAN) | 4032248805884 |
| Qty. | 1 pc(s). |

Creation date December 1, 2023 4:25:22 PM CET

Catalogue status 24.11.2023 / We reserve the right to make technical changes.

FPL 4G2.5/PD/F/3+3

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight 1,047 g

Technical specifications for cable

| | | | |
|------------------------------|------------|----------------------------------|-------------|
| Bending radius, min., moving | 133.5 mm | Bending radius, min., stationary | 35,6 mm |
| Halogen | Yes | Number of wires | 4 |
| Temperature range, moving | -5...70 °C | Temperature range, stationary | -40...70 °C |

General technical data

Protection degree IP54

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001576 | ETIM 7.0 | EC001576 |
| ETIM 8.0 | EC001576 | ETIM 9.0 | EC001576 |
| ECLASS 9.0 | 27-06-04-02 | ECLASS 9.1 | 27-06-91-90 |
| ECLASS 10.0 | 27-06-04-02 | ECLASS 11.0 | 27-06-04-02 |
| ECLASS 12.0 | 27-06-04-02 | ECLASS 13.0 | 27060402 |

Environmental Product Compliance

| | |
|------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 13ce035c-fa1c-4432-a4df-1b9d07f69a8d |

Approvals

ROHS Conform

Downloads

Catalogues [Catalogues in PDF-format](#)

Data sheet

FPL 4G2.5/PD/F/3+3

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

