

**HDC insert  
HDC HP 250 M 25**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



Crimps provide a electrical and mechanical connection between wire and contact that is both secure and reliable. The optimal crimp connection is gas-tight and corrosion-resistant.

**General ordering data**

Type	HDC HP 250 M 25
Order No.	<a href="#">1079690000</a>
Version	HDC insert, Pin, 3000 V, 250 A, Crimp connection, Size: 250
GTIN (EAN)	4032248841769
Qty.	1 pc(s).

Creation date April 13, 2020 11:35:58 PM CEST

Catalogue status 03.04.2020 / We reserve the right to make technical changes.

**HDC insert  
HDC HP 250 M 25**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data****Dimensions and weights**

Length	82.6 mm	Length (inches)	3.252 inch
Net weight	115.74 g	Diameter	32 mm

**Temperatures**

Limit temperature	-50 °C ... 120 °C
-------------------	-------------------

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
------------	----------------

**General data**

Conductor cross-section	25 mm <sup>2</sup>	Insulating material	Polyamide with fibre optic
Insulation strength	10 <sup>10</sup> Ω	Material	Copper alloy
Pollution severity	PD 2 (PD 3)	Rated current (DIN EN 61984)	250 A
Rated impulse voltage (DIN EN 61984)	15 kV	Rated voltage (DIN EN 61984)	3,000 V
Series	HighPower	Size	250
Surface finish	Silver passivated	Type	Pin
UL 94 flammability rating	V-0	Volume resistance	≤ 0.1 mΩ

**Connection data PE**

Connection type PE	Crimp connection, Screw connection
--------------------	------------------------------------

**Power contact**

Rated current (DIN EN 61984), power contact	250 A	Rated impulse voltage (DIN EN 61984), power contact	15 kV
Rated voltage (DIN EN 61984), power contact	3,000 V	Stripping length, performance contact	24 mm
Type of connection, power contact	Crimp connection		

**Version**

Conductor cross-section, max.	25 mm <sup>2</sup>	Conductor cross-section, min.	25 mm <sup>2</sup>
Material	Copper alloy	Size	250
Stripping length, rated connection	24 mm	Surface finish	Silver passivated
Type of connection	Crimp connection	Volume resistance	≤ 0.1 mΩ
Wire connection cross section AWG, max.	AWG 4		

**Classifications**

ETIM 6.0	EC000796	ETIM 7.0	EC000796
eClass 9.0	27-44-02-04	eClass 9.1	27-44-02-04
eClass 10.0	27-44-02-04		

**Data sheet****HDC insert  
HDC HP 250 M 25**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Technical data****Approvals**

Approvals



ROHS

Conform

**Downloads**

Brochure/Catalogue	<a href="#">CAT 3 HDC 17/18 EN</a> <a href="#">FL FIELDWIRING EN</a>
Engineering Data	<a href="#">EPLAN</a>
Engineering Data	<a href="#">STEP</a>

**HDC insert  
HDC HP 250 M 25**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Drawings**

